

Industrial Duty Handlamps



7 Style Handle

- Molded plug end
- With ground tab for wire guards
- Just add guard



9 Style Handle

- Receptacle in handle
- Molded cord plug
- With ground tab for wire guard
- Just add guard

7 Style Handle Pre-Wired	Cat. #
Handle With 25 Ft #16/3 SOOW Cord & 5-15 Plug - No Switch	7-A25
Handle With 50 Ft #16/3 SOOW Cord & 5-15 Plug - No Switch	7-A50
Handle With 25 Ft #16/3 SOOW Cord & 5-15 Plug - With Switch	7-SA25
Handle With 50 Ft #16/3 SOOW Cord & 5-15 Plug - With Switch	7-SA50

9 Style Handle Pre-Wired	Cat. #
Handle With 25 Ft #16/3 SOOW Cord & 5-15 Plug - No Switch	9-A25
Handle With 50 Ft #16/3 SOOW Cord & 5-15 Plug - No Switch	9-A50
Handle With 25 Ft #16/3 SOOW Cord & 5-15 Plug - With Switch	9-SA25
Handle With 50 Ft #16/3 SOOW Cord & 5-15 Plug - With Switch	9-SA50

Lamp Guards for 7 and 9 Series Handlamps

Closed End Wire Guards						
	104	104-R		118	118-R	
No Reflector	104		104-I	118		118-I
With Reflector		104-R			118-R	
Max Wattage	100W			150W		

Open End Wire Guards							
	107	107-I		119	119-R		150
No Reflector	107	107-I		119		150	150-I
With Reflector			107-R		119-R		
Max Wattage	150W			300W		150W PAR38 or 300W type R	

Note: These open end guards are not certified or listed, per UL 153 Standard. Adding these guards to a handlamp constitutes a product that can't be UL listed.

