



Cut



Medium Duty

These abrasion-resistant gloves offer excellent flexibility and fit with high levels of cut protection

- These HyFlex 11-727 abrasion-resistant gloves have a PU coating for increased comfort. The gloves have excellent flexibility and fit, as well as a secure grip on dry to slightly oily pieces for sure handling in a wide range of environments.
- These high-dexterity HyFlex 11-727 gloves deliver a perfect balance of comfort and sure handling with very good cut resistance.



Industries

- Automotive
- Machinery and Equipment
- Metal fabrication
- Chemical

Applications

- Handling metal sheets & panels
- Handling parts with sharp, rough edges
- Final assembly
- Handling materials with sharp or rough edges
- Assembly & inspection of components
- Applying finish to materials, products
- Maintenance
- Opening furnaces draining pumps valves or lines and crackers BTX process
- Lock smith

HyFlex®

ADVANCED MECHANICAL PROTECTION

11-727

Medium Duty cut resistant gloves

Key Features

- EN Level 4 abrasion protection for extended glove life
- An ultralight fabric and tailored to hand fit, creates the sensation of bare-hand comfort
- The soft ultralight-duty seamless liner breathes to keep hands cool and dry, and offers enhanced flexibility
- Excellent fingertip sensitivity with superior comfort
- Also available in vend pack

Sensitisers

- Natural rubber proteins (in knitwrist elastic)

Only a very small number of users may be sensitized to this ingredient in the glove and hence may develop irritant and/or allergic contact reactions.

Technologies



Performance Standards & Regulatory Compliance



REACH Compliant

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COLO R	PACKAGE
HyFlex® 11-727	Palm Coated, Polyurethane, HPPE, Nylon, Spandex, Knitwrist	15	6, 7, 8, 9, 10	195-276 mm; 7.67-10.86 inches	Grey	• 12 pairs in a bag; 12 bags in a carton



For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306.
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Owensville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2020 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

