

ACTIVARMR®

PERSONAL PROTECTIVE GEAR

80-813

Arc Flash and Cut Protective Glove



Heat



Cut



Medium Duty

Superior flame resistant protection from extreme hazards

- Arc flash resistance, flame resistance and high cut protection in a comfortable ergonomic design
- Industry-leading Arc Flash Hazard/Risk Category 2 design helps protect workers against electrical arc flash hazards
- Exclusive Dupont™ Kevlar® composite yarn provides exceptional cut resistance for safe handling of sharp objects
- Soft foam coating and ergonomic design for outstanding flexibility and a secure grip in a variety of work environments



Industries

- Machinery and Equipment
- Mining
- Oil and gas

Applications

- Job tasks with potential for arc-flash or flash-flame exposure
- De-energized electrical equipment panels
- Electrical equipment operation and switching_NFPA 70E_
- Facility and machinery maintenance
- Handling sharp metal or objects

ACTIVARMR®

PERSONAL PROTECTIVE GEAR

80-813

Arc Flash and Cut Protective Glove

Key Features

- Materials are inherently flame resistant, providing protection even after multiple launderings; Meets FR Testing CGSB 155.20-2000
- Superior arc-flash protection: "Arc Rating (ATPV) = 9.4 cal/cm² Arc Category Level 2 per ASTM F2675-13"
- EN Iso cut level C protection provides the worker the ability to handle sharp parts and materials with confidence
- Outstanding ergonomic design, superior comfort, dexterity and flexibility based on patented technology
- Thin 13g knitted liner with DuPont™ Kevlar® increases productivity and safety performance
- Proprietary soft foam coating ensures a secure grip in wet, oily and dry environments to reduce slippage and tension in the hands
- Also available in vend pack

Technologies



Kevlar

Performance Standards & Regulatory Compliance



EN 388:2016



EN 407



REACH Compliant

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COLO R	PACKA GE
ActivArmr® 80-813	Palm Coated, Neoprene Foam, Glass fiber, Modacrylic, DuPont™ Kevlar®, Knitwrist	13	6, 7, 8, 9, 10, 11	225-260 mm; 8.86-10.24 inches	Black	<ul style="list-style-type: none"> • 12 pairs in a bag; 12 bags in a carton



For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada Inc.
105, rue Lauder
Cowansville (Québec)
Q7001 Torre II,
J2K 2K8, Canada
T: 1 800 363-8340
F: 1 888 267-3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2019 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

