

## Eaton Freedom NEMA motor control starter

**A210M0CB**

**UPC:**782116015504

### **Dimensions:**

- **Height:** X
- **Length:** X
- **Width:** X

**Notes:**For ambient compensated overload relay with auto-reset, add Suffix D.

### **Warranties:**

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### **Specifications:**

- **Series:** A200
- **Type:** Horizontal design
- **Amperage Rating:** 18A
- **Max Hp Rating:** 1 hp at 115V, 2 hp at 230V, 3 hp at 208,240V, 5 hp at 480,600V
- **Number Of Poles:** Three-pole
- **Phase:** Three-phase magnetic
- **Size:** 0

### **Supporting documents:**

- [Eatons Volume 5-Motor Control and Protection](#)
- [Instructions for A200, A210, A250 size 6, two- or three-pole non-reversing or reversing motor controllers](#)
- [Eaton Specification Sheet - A210M0CB](#)

### **Certifications:**

- CSA Certified
- UL Listed

**Product compliance:** No Data

