

Eaton BR thermal magnetic circuit breaker

BRD230240

UPC:786676372251

Dimensions:

- **Height:** 3 IN
- **Length:** 3 IN
- **Width:** 2 IN

Weight:.8 LB

Notes:Non-CTL

Warranties: No Data

Specifications:

- **Type:** Type BR 1-Inch quad circuit breaker
- **Amperage Rating:** (2) 30A, (2) 40A
- **Interrupt Rating:** 10 kAIC
- **Number Of Poles:** Four-pole
- **Voltage Rating:** 120/240 V
- **Main Circuit Breaker:** BR
- **Trip Type:** Independent
- **Wire Size:** #14-4 AWG Cu/Al
- **Used With:** Type BR Loadcenters

Supporting documents:

- [Loadcenters and Circuit Breakers](#)
- [Eatons Volume 1-Residential and Light Commercial](#)
- [Eaton Specification Sheet - BRD230240](#)

Certifications:

- UL 489

Product compliance:

- Federal Specifications Classification W-C375