

## Nylon FME Covers

- Round bottom for custom fit
- Adjustable drawstring with metal-free cord lock
- NFPA-701 fire retardant
- Water repellent
- Print reads FME and the appropriate pipe usage size



Part Number	Depth	Fits Pipes	Flange Size 150 & 300 lb	Package Quantity	Available in
CBFR1-T	4"	1" Tube		50	Orange, Red, Pink, Green
CBFR1	4"	1" NPT		50	
CBFR2	4"	2"		50	
CBFR4	6"	4"		30	
CBFR6	6"	6"	2"	30	
CBFR9	6"	9" (NPT 8")	2.5"-3"	30	
CBFR10	6"	10"	3.5"-4"	30	
CBFR12	6"	12"	5"-6"	20	
CBFR15	6"	15"	8"	20	
CBFR18	6"	18"	10"	20	
CBFR24	10"	24"	12"-14"	20	
CBFR30	10"	30"	16"-18"	20	
CBFR38	10"	38"	24"	10	

Don't let your FME Covers be used for storing parts. See Parts Bags for an alternative to prevent foreign material.

Use uniquely identified collection bins prior to laundering. See FME Cover Hampers.

Laundering information available on request.

\*Elastic Closure

## Vented Nylon FME Covers (Patent No. 7,900,654)

- Hook and loop panel reveals mesh ventilation area
- Vented panel allows pressure to equalize
- 200 denier nylon with urethane backing
- Round bottom for custom fit
- Adjustable drawstring with metal-free cord lock
- NFPA-701 fire retardant
- Water repellent



Part Number	Depth	Fits Pipes	Flange Size 150 & 300 lb	Package Quantity	Available in
CBVFR1-T*	4"	1" Flat		50	Orange, Pink
CBVFR1*	4"	1" NPT		50	
CBVFR2.9	4"	2.9" Flat		50	
CBVFR4	6"	4"		30	
CBVFR6	6"	6"	2"	30	
CBVFR9	6"	9"	2.5"-3"	30	
CBVFR12	6"	12"	5"-6"	20	
CBVFR15	6"	15"	8"	20	
CBVFR18	6"	18"	10"	20	
CBVFR24	10"	24"	12"-14"	20	
CBVFR30	10"	30"	16"-18"	20	
CBVFR38	10"	38"	24"	10	

Used when FME barrier protection is needed but ventilation is also required.

Prevents changes in pressure from blowing off, or sucking in cover.

Vented covers are often used in duct work and on operating electrical equipment that requires ventilation.

\*Elastic Closure