


NOTE: ALL MATERIAL COMPLIANT ROHS STANDARD



TEST REQUEST:


1) 100% OPEN SHORT & MISS WIRE TEST.

TABLE:

NO.	ITEM NO.	CABLE LENGTH	JACKET & MOLDING COLOR
1	90-C5EB-XXGN	XX±XXmm	Green
2	90-C5EB-XXRD	XX±XXmm	Red
3	90-C5EB-XXWH	XX±XXmm	White
4	90-C5EB-XXAH	XX±XXmm	Ash
5	90-C5EB-XXBK	XX±XXmm	Black
6	90-C5EB-XXYL	XX±XXmm	Yellow
7	90-C5EB-XXBL	XX±XXmm	Blue
8	90-C5EB-XXOR	XX±XXmm	Orange

MATERIAL LIST:

NO.	PARTS NAME	SPECIFICATION DESCRIPTION	QT' Y	UN.
③	CABLE CAT. 5	Conductor: 24AWG (7/0.19mm Bare Copper+HD-PE)*4P Jacket: PVC Color (See Table), OD: $\phi 5.5 \pm 0.2$ mm Marking: WELTRON ROHS COMPLIANT ENHANCED 350MHZ PATCH CABLE 24AWG 4PR (UL) TYPE CM 60°C 30V ETL Verified to TIA/EIA 568-B.2 CAT 5E	1	PC
②	Molding	45P PVC Color (See Table)		KG
①	RJ45 PLUG	RJ45 Plug (Transparent), Pin Gold Plated 3u".	2	PCS



Customer	Item NO.: See Table
Title	8P8C PLUG TO 8P8C PLUG CAT5E UTP CABLE
Drawing NO.	Revision A-1
Design	
Check	Date 2012. 08. 29 Tolerance .XX(0.01)
Approved	Units mm 3DR Page 1/1