

CHROME SLT®

Slipfit® cuff assists a quick on and off between tasks

Goatskin leather palm provides a traditional style of comfort

Aramid liner for 360° cut protection (interior layer)

Grip in dry or light oil situations

Form-fitting, quality materials







Back-of-hand impact protection

High dexterity



4060 Chrome SLT®

PROTECTION ZONES:

 Impact Protection	 Aramid Liner	ANSI/ISEA CUT	GRAM SCORE
		A5	2509
  2X22EP			
<ul style="list-style-type: none"> • Lab tested in accordance with EN407 contact heat for a level 2 performance • Lab tested in accordance with ANSI/ISEA 105 Conductive Heat for a level 2 performance • Lab tested in accordance with HRC ATPV: 23.6 Cal/cm² for a level 2 performance 			

FEATURES:

HexArmor® Chrome SLT® gloves are built for a wide array of applications. Each product in the series was crafted to fit the hand with a specific purpose. With multiple styles and various safety features, you can be confident that the Chrome SLT® will keep your hands protected against almost any hazard. Our Chrome SLT® gloves were designed with ultimate comfort in mind, providing unsurpassed dexterity while maintaining cut and puncture resistance.

ATTRIBUTES:

Style:	Mechanics
Grip:	Dry or light oil
Cuff Style:	SlipFit®
Sizes:	6/XS through 12/3XL

HexArmor®

Call **1-877-MY ARMOR** or visit **hexarmor.com**

HexArmor® products are cut and puncture resistant, NOT CUT AND PUNCTURE PROOF. Do not use with moving or serrated blades or tools. User shall be exclusively responsible to assess the suitability of the product as specified for any individual application or use. Protection zones are to be used as a general guide. Actual product protection zones may differ. Product features, design, protection zones subject to change.

Protected by patents and patents pending