

# ALASTA® 100 & 200

Nitrile exam gloves



## Extreme Comfort, Precision Fit

Market leader for over 15 years



- Comfortable precision fit, reliable strength
- Available in 100 and 200 glove count boxes
- Chemotherapy drug rated†
- Tested against fentanyl



"Love These Gloves!"

I've been using these gloves for 17 years and I love them! They fit my hands perfect."

– Traci

# Alasta<sup>®</sup>

Soft Fit™ Nitrile Gloves

Featuring Soft Fit™ thin nitrile technology, Alasta<sup>®</sup> medical exam gloves are comfortable, provide a precision fit and holds up during longer wear times.



PRODUCT DETAILS	
Material	Nitrile
Interior	Powder Free
Grade	Medical Examination
Watertight Test	1.5 AQL
Color	Violet Blue
Texture	Finger

PHYSICAL PROPERTIES (TYPICAL VALUES*)	
Palm Thickness	0.06 mm   2.4 mil
Finger Thickness	0.08 mm   3.1 mil
Length	245 mm   9.6 in
Tensile Strength (MPA)	35
Elongation %	545

ORDER INFORMATION	
Product Number	ALS100 ALS200
Available Sizes	XS, S, M, L, XL
Glove Count	100/box   10 boxes/case 200/box   10 boxes/case

CERTIFICATIONS	
Chemotherapy Drug Tested†	Yes
Tested Against Fentanyl	Yes
PFAS	Yes
BPA Free	Yes

PRODUCT CONFORMANCE
ASTM D6319, ASTM D6978 (Chemo and Fentanyl), ASTM D5151, ASTM D6124

RECOMMENDED INDUSTRIES
Dental, Healthcare, Laboratory, Industrial Safety, Automotive, Veterinarian

PERFORMANCE LEVEL	LIGHT DUTY	HIGH TACTILITY	MID DUTY	HEAVY DUTY	HIGH RISK
CUSTOMER NEED/ APPLICATION	Basic Barrier Coverage	Best Touch Sensitivity	Broad Range of Uses	Increased Durability	Longer Cuff Length
	Lowest cost option	Delivers a second skin feel	Perfect for a variety of applications	Great for more rugged applications	Used in higher risk settings



800-523-2055 | DASHMEDICAL.COM

\*Typical values have an allowable specification variance  
†Contact DASH Medical for a list of tested Chemotherapy drugs

DASH\_SS\_ALS\_05.2022