

HALO®

Nitrile exam gloves



Jack of All Trades



- Soft 'rubber' like feel
- Durable, puncture resistant
- Latex free
- Powder free
- Textured fingers



"Best I Have Found!"

I have been using Halo gloves for about two years. They are thicker than standard nitrile/vinyl, yet not as thick as some other heavier gloves (a good thing) and I retain my 'finger feeling' yet stay completely protected. A nice product."

– ALEX2222



Halo is the ideal choice for a wide variety of applications. Flexible nitrile formulation delivers a durable barrier with a soft feel.



PRODUCT DETAILS	
Material	Nitrile
Interior	Powder Free
Grade	Medical Examination
Watertight Test	1.5 AQL
Color	Light Blue
Texture	Full

PHYSICAL PROPERTIES (TYPICAL VALUES*)	
Palm Thickness	0.08 mm 3.1 mil
Finger Thickness	0.10 mm 3.9 mil
Length	230 mm 9.1 in
Tensile Strength (MPA)	18
Elongation %	500

ORDER INFORMATION	
Product Number	HAL100
Available Sizes	XS, S, M, L, XL
Glove Count	100/box 10 boxes/case

CERTIFICATIONS	
Chemotherapy Drug Tested†	Yes
Tested Against Fentanyl	Yes
PFAS Free	Yes

PRODUCT CONFORMANCE
ASTM D6319, ASTM D6978 (Chemo), ASTM D5151, ASTM D6124

RECOMMENDED INDUSTRIES
Laboratory, Industrial Safety, Automotive, Janitorial, Veterinarian

PERFORMANCE LEVEL	LIGHT DUTY	HIGH TACTILITY	MID DUTY	HEAVY DUTY	HIGH RISK
CUSTOMER NEED/ APPLICATION	Basic Barrier Coverage	Best Touch Sensitivity	Broad Range of Uses	Increased Durability	Longer Cuff Length
	Lowest cost option	Delivers a second skin feel	Perfect for a variety of applications	Great for more rugged applications	Used in higher risk settings



800-523-2055 | DASHMEDICAL.COM

*Typical values have an allowable specification variance
†Contact DASH Medical for a list of tested Chemotherapy drugs