

# VitalGard®

Nitrile exam gloves



Gold Standard for Comfort and Reliability



- Aggressively priced
- Puncture and tear resistant
- Latex free
- Finger textured



## "Great Purchase..."

These gloves work perfectly for our needs! Can't beat the price!"

– DASH Website Review

# VITAL GARD®

## NITRILE EXAMINATION GLOVES

With so many choices in hand protection these days maybe you just want to keep it simple – low cost, high quality. VitalGard® nitrile gloves are your answer.



PRODUCT DETAILS	
Material	Nitrile
Interior	Powder Free
Grade	Medical Examination
Watertight Test	1.5 AQL
Color	Periwinkle Blue
Texture	Finger

PHYSICAL PROPERTIES (TYPICAL VALUES*)	
Palm Thickness	0.07 mm   2.8 mil
Finger Thickness	0.10 mm   3.9 mil
Length	240 mm   9.5 in
Tensile Strength (MPA)	28
Elongation %	540

ORDER INFORMATION	
Product Number	VNPF100
Available Sizes	XS, S, M, L, XL, XXL
Glove Count	100/box 10 boxes/case

CERTIFICATIONS	
Chemotherapy Drug Tested†	Yes
Tested Against Fentanyl	No
PFAS Free	Yes

PRODUCT CONFORMANCE
ASTM D6319, ASTM D5151, ASTM D6124, ASTM D6978 (Chemo)

RECOMMENDED INDUSTRIES
Dental, Healthcare, Laboratory, Industrial Safety, Automotive, Veterinarian

PERFORMANCE LEVEL	LIGHT DUTY	HIGH TACTILITY	MID DUTY	HEAVY DUTY	HIGH RISK
CUSTOMER NEED/ APPLICATION	Basic Barrier Coverage	Best Touch Sensitivity	Broad Range of Uses	Increased Durability	Longer Cuff Length
	Lowest cost option	Delivers a second skin feel	Perfect for a variety of applications	Great for more rugged applications	Used in higher risk settings



\*Typical values have an allowable specification variance  
†Contact DASH Medical for a list of tested Chemotherapy drugs