












# Round Head Slotted/Phillips (Combo) Machine Screws - Zinc Plated - PC 4000

Round head machine screws project above the material surface. This head style is used when clearance is not an important factor. Length is determined from the base of the fastener head.

- Machine Screws
- Round Head
- Slotted/Phillips
- Zinc Plated Steel
- Invincibox™ Up To 2"

CAT NO	UPC	SIZE	STD	SLEEVE	MSTR	WT/STD	UNIT
RMC63212	55820	6-32 x 1/2	100	500	4000	0.20#	C
RMC63234	55822	6-32 x 3/4	100	500	4000	0.26#	C
RMC6321	55824	6-32 x 1	100	500	4000	0.37#	C
RMC632114	55825	6-32 x 1-1/4	100	500	4000	0.40#	C
RMC632112	55826	<b>6-32</b> 6-32 x 1-1/2	100	500	4000	0.49#	C
RMC6322	55827	6-32 x 2	100	500	3000	0.62#	C
RMC632212	55821	6-32 x 2-1/2	100	500	1000	0.75#	C
RMC6323	55823	6-32 x 3	100	500	1000	0.92#	C
<hr/>							
RMC83212	55840	8-32 x 1/2	100	500	4000	0.29#	C
RMC83234	55842	8-32 x 3/4	100	500	4000	0.40#	C
RMC8321	55844	8-32 x 1	100	500	4000	0.50#	C
RMC832114	55845	8-32 x 1-1/4	100	500	4000	0.72#	C
RMC832112	55846	<b>8-32</b> 8-32 x 1-1/2	100	500	3000	0.82#	C
RMC8322	55847	8-32 x 2	100	500	3000	1.03#	C
RMC832212	55880	8-32 x 2-1/2	100	500	1000	1.25#	C
RMC8323	55884	8-32 x 3	100	500	1000	1.52#	C
<hr/>							
RMC102412	55860	10-24 x 1/2	100	500	4000	0.65#	C
RMC102434	55862	10-24 x 3/4	100	500	4000	0.66#	C
RMC10241	55864	<b>10-24</b> 10-24 x 1	100	500	4000	0.80#	C
RMC1024114	55865	10-24 x 1-1/4	100	500	3000	0.83#	C
RMC1024112	55866	10-24 x 1-1/2	100	500	3000	1.04#	C
RMC10242	55867	10-24 x 2	50	250	1500	1.38#	C
RMC10243	55869	10-24 x 3	100	500	3000	1.98#	C
<hr/>							
RMC103212	55870	10-32 x 1/2	100	500	4000	0.40#	C
RMC103234	55872	10-32 x 3/4	100	500	4000	0.69#	C
RMC10321	55874	<b>10-32</b> 10-32 x 1	100	500	4000	0.82#	C
RMC1032114	55875	10-32 x 1-1/4	100	500	3000	0.99#	C
RMC1032112	55876	10-32 x 1-1/2	100	500	3000	1.15#	C
RMC10322	55877	10-32 x 2	50	250	1500	0.72#	C
<hr/>							
RMC1438	55801	1/4 x 3/8	100	500	3000	0.88#	C
RMC1412	55800	1/4 x 1/2	100	500	3000	1.04#	C
RMC1434	55802	1/4 x 3/4	100	500	3000	1.21#	C
RMC141	55804	1/4 x 1	100	500	3000	1.51#	C
RMC14114	55805	1/4 x 1-1/4	100	500	3000	1.76#	C
RMC14112	55806	<b>1/4-20</b> 1/4 x 1-1/2	50	250	1500	1.02#	C
RMC142	55807	1/4 x 2	50	250	1500	1.27#	C
RMC14212	55812	1/4 x 2-1/2	100		1000	2.92#	C
RMC143	55813	1/4 x 3	100		1000	3.43#	C
RMC144	55814	1/4 x 4	100		1000	4.59#	C
<hr/>							
RMC3834	55832	3/8 x 3/4	100		1000	4.25#	C
RMC381	55833	3/8 x 1	100		1000	4.28#	C
RMC38114	55834	3/8 x 1-1/4	100		1000	4.77#	C
RMC38112	55835	3/8 x 1-1/2	100		1000	5.22#	C
RMC382	55836	<b>3/8-16</b> 3/8 x 2	100		1000	6.41#	C
RMC38212	55837	3/8 x 2-1/2	100		400	7.57#	C
RMC383	55838	3/8 x 3	50		400	4.22#	C
RMC384	55839	3/8 x 4	50		400	5.01#	C
<hr/>							
RMCT6321	55828	<b>6-32 Tuff Pack</b> 6-32 x 1	500		3000	2.04#	C
RMCT632114	55829	 6-32 x 1-1/4	500		3000	2.46#	C
RMCT632112	55830	 6-32 x 1-1/2	500		3000	2.72#	C
RMCT6322	55831	 6-32 x 2	300		1800	2.11#	C
<hr/>							
RMCT8321	55848	<b>8-32 Tuff Pack</b> 8-32 x 1	500		3000	3.05#	C
RMCT832114	55849	 8-32 x 1-1/4	500		3000	3.65#	C
RMCT832112	55850	 8-32 x 1-1/2	500		3000	4.09#	C
RMCT8322	55851	 8-32 x 2	300		1800	3.20#	C
<hr/>							
RMCT141	55808	<b>1/4-20 Tuff Pack</b> 1/4 x 1	300		1800	7.69#	C
RMCT14114	55809	 1/4 x 1-1/4	300		1800	9.42#	C
RMCT14112	55810	 1/4 x 1-1/2	250		1500	5.03#	C
RMCT142	55811	 1/4 x 2	150		900	3.73#	C

