



GE
Lighting

68051 - F35/CW/C/U6/WM

F35/CW/C/U6/WM

Product Photo



GENERAL CHARACTERISTICS

Base Description	Medium Bi-Pin
Base Type	Pin/Plug-In
Mercury Content	30 mg
Mercury-Picogram per mean lm hr	1530.6
Starting Temp (MIN) C-degrees	15 °C
Bulb Material	Sodalime glass
Rated Life Hours-nominal	14000 h
Primary Application	Energy Saving
Product Technology	Linear Fluorescent
Base	G13
Bulb Shape	T12

PHOTOMETRIC CHARACTERISTICS

Mean Lumens nominal	1400 lm
Nominal Initial Lumen per Watt	47
Initial Lumens-nominal	1650 lm
Color Rendering Index-CRI	87
Color Temperature	4100 K

PRODUCT INFORMATION

Product Code	68051
Description	F35/CW/C/U6/WM
Alternative Unit Of Measure	CASE

DIMENSIONS

Diameter	1.5 in
Nominal Length	22.5 in

ELECTRICAL CHARACTERISTICS

Rated power (Watts)	35 W
---------------------	------