

Heavy-Duty Bulk Nylon Line

- Use with line carriers for any size conduit.
- Doubles as general-purpose line for layout of suspended ceilings, plumb-lines and masonry construction.
- All packages are center-dispensing (except #LP1707).

Catalog Number	Description	Length (ft.)	Breaking Strength (lbs.)	Package Quantity
LP1701	Heavy-duty Bulk Nylon Line	1000'	100	Box of 6
LP1702	Heavy-duty Bulk Nylon Line	2000'	30	Box of 6
LP1703	Heavy-duty Bulk Nylon Line	1400'	22	Box of 5
LP1707	Heavy-duty Bulk Nylon Line	1350'	100	Box of 6
LP1722	Heavy-duty Bulk Nylon Line	2200'	90	Box of 6
LP1702B	Heavy-duty Bulk Nylon Line	2000'	30	Bag of 1
LP1701B	Heavy-duty Bulk Nylon Line	1000'	100	Bag of 1



Poly-Pull™ Series Pull Line

- Super high strength — up to 500 lbs. breaking strength.
- Self-lubricated polyolefin line lasts for years; will not rust, rot or mildew.
- Center-dispensing box pays out line smoothly.
- Blow directly into conduit using Dial-A-Line™ Seal-off bodies.

Catalog Number	Description	Length	Breaking Strength (lbs.)	Outside Diameter	Color
PL102	Poly-Twine™ Pull Line	6500'	190	1/8"	Yellow
PL102B	Poly-Twine™ Pull Line in bucket	6500'	190	1/8"	Yellow
PL231	Poly-Pull™ Line in roll	1000'	100	1/16"	White
PL232	Poly-Pull™ Line in dispenser box	6500'	200	1/8"	Blue tracer
PL232B	Poly-Pull™ Line in bucket	6500'	200	1/8"	Blue tracer
PL235	Poly-Pull™ Line in dispenser box	2200'	500	3/16"	Red tracer
PL235B	Poly-Pull™ Line in bucket	2200'	500	3/16"	Red tracer
*PL232BB	*Poly-Pull™ Line in bucket	6500'	200	1/8"	Blue tracer

*minimum purchase quantity of 72



Conduit Measuring Tape

- The most accurate method of measuring in-place conduit runs. Blow or vacuum through the run to estimate wire length or to locate obstructions. Marked in one-foot increments.
- Strong and durable. True Tape™ has breaking strength of 45 lbs.; Super True Tape™ has breaking strength of 165 lbs. Both are mildew- and rot-resistant.

Catalog Number	Description	Dimensions
TT31	True Tape™ Measuring Tape	3000 ft. Roll x .25" wide
ST40	Super True Tape™ Conduit Measuring Tape	2750 ft. on Roll

Note: Cannot be used with Gunslinger™

