

**7 PIECE 3/8" DRIVE LONG BALL
HEX BIT SOCKET SET**

Item #: HLB-9407S

• Weight (lbs): 1.08



Contents	Size (in)	Overall Length (in)
HLB-9418-2	1/8	6-1/8
HLB-9419-2	5/32	6-1/8
HLB-9420-2	3/16	6-7/64
HLB-9421-2	7/32	6-1/8
HLB-9422-2	1/4	6-9/64
HLB-9423-2	5/16	6-7/64
HLB-9424-2	3/8	6-7/64
Clip Rail		

**8 PIECE 3/8" DRIVE LONG BALL METRIC
HEX BIT SOCKET SET**

Item #: HLB-9408MS

• Weight (lbs): 1.38



Contents	Size (mm)	Overall Length (in)
HLB-9403M-2	3 mm	6-7/64
HLB-9404M-2	4 mm	6-1/8
HLB-9405M-2	5 mm	6-1/8
HLB-9406M-2	6 mm	6-7/64
HLB-9407M-2	7 mm	6-7/64
HLB-9408M-2	8 mm	6-9/64
HLB-9409M-2	9 mm	6-1/8
HLB-9410M-2	10 mm	6-9/64
Clip Rail		

**7 PIECE 3/8" DRIVE SLOTTED/PHILLIPS®
BIT SOCKET SET**

Item #: HW-9507S

• Weight (lbs): 0.59



Contents	Size	Overall Length (in)
HW-9450-2	#1	1-13/16
HW-9451-2	#2	1-53/64
HW-9452-2	#3	1-53/64
HW-9453-2	#4	1-53/64
HW-9504-2	3/16	1-53/64
HW-9505-2	1/4	1-53/64
HW-9506-2	5/16	1-27/32
Clip Rail		



3/8" DRIVE DEEP SOCKETS - 12 POINT



Size (in)	Drive End Diameter (in)	Working End Diameter (in)	Overall Length (in)	Weight (lbs)	Item No.
3/8	21/32	9/16	1-51/64	0.09	30412
7/16	41/64	41/64	1-51/64	0.09	30414
1/2	23/32	23/32	1-51/64	0.12	30416
9/16	13/16	13/16	2	0.16	30418
5/8	55/64	55/64	2-3/32	0.18	30420
11/16	15/16	15/16	2-13/64	0.23	30422
3/4	1-1/64	1-1/64	2-13/64	0.25	30424
13/16	1-3/32	1-3/32	2-1/2	0.32	30426
7/8	1-11/64	1-11/64	2-1/2	0.38	30428
15/16	1-1/4	1-1/4	2-1/2	0.47	30430
1	1-21/64	1-21/64	2-1/2	0.52	30432

ASME B107.1

3/8" DRIVE METRIC DEEP SOCKETS - 12 POINT



Size (mm)	Drive End Diameter (in)	Working End Diameter (in)	Overall Length (in)	Weight (lbs)	Item No.
7 mm	21/32	7/16	2-9/64	0.10	HW-1607M
8 mm	21/32	15/32	2-1/8	0.10	HW-1608M
9 mm	21/32	33/64	2-1/8	0.11	HW-1609M
10 mm	21/32	37/64	2-9/64	0.11	HW-1610M
11 mm	21/32	21/32	2-1/8	0.12	HW-1611M
12 mm	45/64	45/64	2-9/64	0.12	HW-1612M
13 mm	23/32	23/32	2-9/64	0.16	HW-1613M
14 mm	25/32	25/32	2-9/64	0.16	HW-1614M
15 mm	55/64	55/64	2-3/4	0.24	HW-1615M
16 mm	55/64	55/64	2-3/4	0.24	HW-1616M
17 mm	15/16	15/16	2-3/4	0.27	HW-1617M
18 mm	15/16	15/16	2-49/64	0.27	HW-1618M
19 mm	1-1/64	1-1/64	2-49/64	0.31	HW-1619M

ASME B107.5M



3/8" DRIVE HEX BIT SOCKETS

• Zinc phosphate finish on bits. Pressed In, Foreign Object Debris (FOD) Compliant. Easy to read stamped markings.



Size (in)	Overall Length		Item No.
	(in)	Weight (lbs)	
1/16	1-51/64	0.06	HW-9438-2
5/64	1-13/16	0.06	HW-9439-2
3/32	1-53/64	0.06	HW-9440-2
7/64	1-13/16	0.06	HW-9441-2
1/8	1-13/16	0.07	HW-9442-2
9/64	1-53/64	0.07	HW-9443-2
5/32	1-53/64	0.07	HW-9444-2
3/16	1-53/64	0.08	HW-9449-2
7/32	1-13/16	0.09	HW-9448-2
1/4	1-13/16	0.09	HW-9447-2
5/16	1-13/16	0.10	HW-9446-2
3/8	1-13/16	0.14	HW-9445-2

3/8" DRIVE METRIC HEX BIT SOCKETS

• Zinc phosphate finish on bits. Pressed In, Foreign Object Debris (FOD) Compliant. Easy to read stamped markings.



Size (mm)	Overall Length		Item No.
	(in)	Weight (lbs)	
2 mm	1-51/64	0.06	HW-9402M-2
2.5 mm	1-51/64	0.06	HW-94025M-2
3 mm	1-51/64	0.06	HW-9403M-2
4 mm	1-51/64	0.06	HW-9404M-2
5 mm	1-51/64	0.08	HW-9405M-2
6 mm	1-51/64	0.09	HW-9406M-2
7 mm	1-51/64	0.09	HW-9407M-2
8 mm	1-51/64	0.10	HW-9408M-2
9 mm	1-13/16	0.13	HW-9409M-2
10 mm	1-51/64	0.14	HW-9410M-2
11 mm	1-51/64	0.15	HW-9411M-2
12 mm	1-13/16	0.15	HW-9412M-2

3/8" DRIVE LONG BALL HEX BIT SOCKETS

• Zinc phosphate finish on bits. Pressed In, Foreign Object Debris (FOD) Compliant. Easy to read stamped markings.



Size (in)	Overall Length		Item No.
	(in)	Weight (lbs)	
1/8	6-1/8	0.09	HLB-9418-2
5/32	6-1/8	0.10	HLB-9419-2
3/16	6-7/64	0.12	HLB-9420-2
7/32	6-1/8	0.14	HLB-9421-2
1/4	6-9/64	0.15	HLB-9422-2
5/16	6-7/64	0.19	HLB-9423-2
3/8	6-7/64	0.29	HLB-9424-2

14MM SOCKETS

3/8" DRIVE HEX BIT SOCKETS



3/8" DRIVE LONG BALL METRIC HEX BIT SOCKETS

• Zinc phosphate finish on bits. Pressed In, Foreign Object Debris (FOD) Compliant. Easy to read stamped markings.



Size (mm)	Overall Length		Item No.
	(in)	Weight (lbs)	
3 mm	6-7/64	0.09	HLB-9403M-2
4 mm	6-1/8	0.11	HLB-9404M-2
5 mm	6-1/8	0.12	HLB-9405M-2
6 mm	6-7/64	0.15	HLB-9406M-2
7 mm	6-7/64	0.17	HLB-9407M-2
8 mm	6-9/64	0.20	HLB-9408M-2
9 mm	6-1/8	0.25	HLB-9409M-2
10 mm	6-9/64	0.29	HLB-9410M-2

3/8" DRIVE SLOTTED SCREWDRIVER BIT SOCKETS

• Zinc phosphate finish on bits. Pressed In, Foreign Object Debris (FOD) Compliant. Easy to read stamped markings.



Size (in)	Overall Length		Item No.
	(in)	Weight (lbs)	
3/16	1-53/64	0.08	HW-9504-2
1/4	1-53/64	0.08	HW-9505-2
5/16	1-27/32	0.09	HW-9506-2

3/8" DRIVE PHILLIPS® BIT SOCKETS

• Zinc phosphate finish on bits. Pressed In, Foreign Object Debris (FOD) Compliant. Easy to read stamped markings.



Size	Overall Length		Item No.
	(in)	Weight (lbs)	
#1	1-13/16	0.08	HW-9450-2
#2	1-53/64	0.08	HW-9451-2
#3	1-53/64	0.09	HW-9452-2
#4	1-53/64	0.09	HW-9453-2



1/2" DRIVE 9 PIECE STANDARD DEEP SOCKET SET

Item #: 309-BS

• Weight (lbs): 3.6



Contents	Size (in)	Overall Length (in)	Point Count
40416	1/2	3-3/32	6
40418	9/16	3-3/32	6
40420	5/8	3-3/32	6
40422	11/16	3-3/32	6
40424	3/4	3-3/32	6
40426	13/16	3-3/32	6
40428	7/8	3-3/32	6
40430	15/16	3-3/32	6
40432	1	3-3/32	6
Clip Rail			

1/2" DRIVE 7 PIECE HEX BIT SOCKET SET - SAE

Item #: HW-9607S

• Weight (lbs): 1.89



Contents	Size (in)	Overall Length (in)
HW-9606-2	5/16	2-1/2
HW-9607-2	3/8	2-1/2
HW-9608-2	7/16	2-1/2
HW-9609-2	1/2	2-1/2
HW-9610-2	9/16	2-1/2
HW-9611-2	5/8	2-1/2
HW-9612-2	3/4	2-1/2
Clip Rail		

1/2" DRIVE 8 PIECE METRIC SOCKET SET

Item #: 308-M

• Weight (lbs): 1.6



Contents	Size (mm)	Overall Length (in)	Point Count
42010M	10 mm	1-1/2	6
42011M	11 mm	1-1/2	6
42012M	12 mm	1-1/2	6
42013M	13 mm	1-1/2	6
42014M	14 mm	1-1/2	6
43015M	15 mm	1-1/2	6
43017M	17 mm	1-1/2	6
43019M	19 mm	1-1/2	6
Clip Rail			

1/2" DRIVE 7 PIECE HEX BIT SOCKET SET - METRIC

Item #: HW-9507MS

• Weight (lbs): 1.88



Contents	Size (mm)	Overall Length (in)
HW-9606M-2	6 mm	2-1/2
HW-9608M-2	8 mm	2-1/2
HW-9610M-2	10 mm	2-1/2
HW-9612M-2	12 mm	2-1/2
HW-9614M-2	14 mm	2-1/2
HW-9617M-2	17 mm	2-1/2
HW-9619M-2	19 mm	2-1/2
Clip Rail		

