



MCR
SAFETY

9672

Memphis

Cut Protection

Specification Sheet

PRODUCT DESCRIPTION:

Dyneema® is extremely cool to work in and it offers the best abrasion resistance of the high performance fibers. The Memphis Dyneema® offerings vary in a seamless shell that provides abrasion, tear and cut protection. The various palm and finger coatings enhance grip and wear. The 9672 Memphis Dyneema® PU provides a 13 gauge salt and pepper DSM Certified Dyneema shell with gray PU palm and fingertip coating.

FEATURES:

- 13 gauge salt and pepper DSM Certified Dyneema® shell
- Gray PU coated palm and fingertips
- CE 4341
- ANSI Cut Level 2

APPLICATIONS:

Automotive Assembly, Farming, Landscaping, Material Handling, Glass handling, HVAC, Bakeries



TECHNICAL DATA FOR: 9672

Brand	Memphis Gloves
Series	Memphis
Product Type	Cut Protection
Size	Large
Gauge	13 Gauge
Material Group	Strings
Material	Dyneema

EN 388 : CE Score - Abrasion	4
EN 388 : CE Score - Cut	3
EN 388 : CE Score - Tear	4
EN 388 : CE Score - Puncture	1

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2016 MCR Safety - All Rights Reserved




MCR
SAFETY

9672

Memphis

Cut Protection Specification Sheet



Item No:	Size:	A:	B:	C:	Case Weight	UOM Weight
9672L	Large	13.39	4.64	3.35	23.784 lb.	1.982
9672M	Medium	12.80	4.72	3.15	21.744 lb.	1.812
9672S	Small	12.40	4.20	3.15	19.632 lb.	1.636
9672XL	X - Large	13.79	5.03	3.35	25.272 lb.	2.106
9672XS	X - Small	11.80	3.93	2.95	18.420 lb.	1.535
9672XXL	XX - Large	14.18	5.19	3.35	26.676 lb.	2.223

MCR Safety - 1255 Schilling Blvd. W. - Collierville, TN 38017 - USA

Phone: 901-795-5810 - Toll Free: 800-955-6887 - Fax: 800-999-3908 - Web: www.mcrcsafety.com

©2016 MCR Safety - All Rights Reserved