

NetRunner™ Vertical Cable Management

- Large finger openings accommodate up to 24 Category 6 cables
- Integral cable retainers on the end of each finger to help contain cables within each rack unit
- Bend radius fingers align with rack spaces to support cables as they transition to the vertical pathway
- Dual hinged covers can be opened 110° to the left or right to provide complete access to the cables inside the vertical pathway
- Snap-on cable retainers can be placed on to fingers to help retain cables in channel during installation and maintenance
- Vertical managers include hinged covers, cable retainers, mounting brackets and #12-24 screws



WMPV22E

WMPVF22E

| Part Number | Part Description | No. of Rack Spaces [^] | Std. Pkg. Qty. | Std. Ctn. Qty. |
|---|---|---------------------------------|----------------|----------------|
| Vertical Cable Managers – Front and Rear | | | | |
| WMPV22E | Front and rear vertical manager. Dimensions: 41.5"H x 4.9"W x 12.0"D (1054mm x 125mm x 306mm) | 22 | 1 | — |
| WMPVHC45E | Front and rear vertical manager. Dimensions: 83.0"H x 6.7"W x 14.1"D (2108mm x 170mm x 357mm) | 45 | 1 | — |
| WMPV45E | Front and rear vertical manager. Dimensions: 83.0"H x 4.9"W x 12.0"D (2108mm x 125mm x 306mm) | 45 | 1 | — |
| Vertical Cable Managers – Front Only | | | | |
| WMPVF22E | Front only vertical manager. Dimensions: 41.5"H x 4.9"W x 6.5"D (1054mm x 125mm x 165mm) | 22 | 1 | — |
| WMPVHCF45E | Front only vertical manager. Dimensions: 83.0"H x 6.7"W x 7.6"D (2108mm x 170mm x 192mm) | 45 | 1 | — |
| WMPVF45E | Front only vertical manager. Dimensions: 83.0"H x 4.9"W x 6.5"D (2108mm x 125mm x 165mm) | 45 | 1 | — |
| Accessories | | | | |
| WMPVCBE | NetRunner™ Center Mount Bracket Kit allows mounting to adjacent racks. Four brackets per kit. | — | 1 | 10 |
| WMPVSMK | NetRunner™ Side Mount Hardware Kit for use with Panduit CMR19X84S racks and Panduit R4P 4 post rack series. | — | 1 | 10 |
| WMPVCMB | Rack adapter bracket kit. Front or back mounted on racks with dimensions up to 1 5/8" (41.1mm) from outside edge of rack to center of the mounting hole. Two kits are required for center mounting of NetRunner™ Managers. Four brackets per kit. | — | 1 | 10 |
| NREP | End panel for use with NRV series, WMPVHCF45E/WMPVHC45E. Includes two panel sections to cover 45 RU on one side. | — | 1 | — |
| WMPV45EP | End panel for use with WMPV45E. Includes two panel sections to cover 45 RU on one side. | — | 1 | — |
| WMPV45ERTW | Rack top trough with waterfall creates pathway above rack, for use with CMR19X84 and WMPV45E/WMPVHC45E and NRV series. | — | 1 | — |
| WR5E-X | Snap-on finger cable retainers. | — | 10 | 100 |

[^]One rack space = 1.75" (44.45mm).

All product color is black.

| Part Number | Cable Capacity Chart | | | | | | | |
|-------------------|----------------------|------|----------------|------|--------------|------|---------------|------|
| | Cat6A-SD (.240") | | Cat 6A (.300") | | Cat6 (.240") | | Cat5e (.225") | |
| | Front | Rear | Front | Rear | Front | Rear | Front | Rear |
| WMPV22E | 143 | 143 | 91 | 143 | 143 | 143 | 162 | 162 |
| WMPVF22E | 143 | — | 91 | — | 143 | — | 162 | — |
| WMPV45E | 143 | 143 | 91 | 143 | 143 | 143 | 162 | 162 |
| WMPVF45E | 143 | — | 91 | — | 143 | — | 162 | — |
| WMPVHC45E | 266 | 266 | 170 | 266 | 266 | 266 | 303 | 303 |
| WMPVHCF45E | 266 | — | 170 | — | 266 | — | 303 | — |

Note: Capacities are based upon a fill rate of 35% to accommodate proper cable routing techniques.

For comparison, multiply by 1.5 for a fill rate of 50%.