

## Eaton QC thermal magnetic circuit breaker

QHCX2020T

UPC:782116103720

### Dimensions:

- **Height:** 2 IN
- **Length:** 3 IN
- **Width:** 3 IN

**Weight:** .7 LB

### Warranties:

- 1 year

### Specifications:

- **Type:** Miniature circuit breaker
- **Special Features:** Ring or Spade Lug Terminals
- **Amperage Rating:** 20A
- **Interrupt Rating:** 42 kAIC
- **Number Of Poles:** Two-pole
- **Voltage Rating:** 120/240 V
- **Trip Type:** Thermal-magnetic
- **Connection:** Cable-in/cable-out
- **Circuit Breaker Type:** QHCX
- **Terminals:** Ring or spade lug terminals
- **Options:** Non-interchangeable

### Supporting documents:

- [Loadcenters and Circuit Breakers](#)
- [Eatons Volume 4-Circuit Protection](#)
- [Eaton Specification Sheet - QHCX2020T](#)

### Certifications:

- UL Listed
- CSA Certified

**Product compliance:** No Data



