

THHN - DUAL RATED 90 DEGREE C DRY/75 DEGREE C WET - STRANDED



Catalog Number	Item No	Description	Approx. Net Lbs. Per 1000 Ft.	Size	Per 1000 Ft.			
					Col. A	Col. B	Col. C	
10	23031	--	38	10	284.08	156.24	142.04	
8	23104	--	63	8	462.20	254.21	231.10	
6	13151	--	95	6	730.58	401.82	365.29	
4	13201	--	152	4	1108.14	609.48	554.07	
3	23257	--	188	3	1372.04	754.62	686.02	
2	23307	--	234	2	1720.00	946.00	860.00	+
1	23351	--	299	1	2174.62	1196.04	1087.31	
1/0	23401	--	371	1/0	2626.40	1444.52	1313.20	
2/0	23406	--	461	2/0	3225.74	1774.16	1612.87	
3/0	23411	--	574	2/0	3988.88	2193.88	1994.44	
4/0	23416	--	717	4/0	5032.62	2767.94	2516.31	
250KCM	23421	--	850	250KCM	6149.46	3382.20	3074.73	
300KCM	23426	--	1011	300KCM	7259.68	3992.82	3629.84	
350KCM	23431	--	1172	350KCM	8403.24	4621.78	4201.62	
400KCM	23436	--	1333	400KCM	9958.26	5477.04	4979.13	
500KCM	23441	--	1653	500KCM	11697.38	6433.56	5848.69	
600KCM ¹	23446	--	1985	600KCM	1420.86	781.47	710.43	
750KCM ¹	23451	--	2462	750KCM	1895.26	1042.39	947.63	
1000KCM ¹	23458	--	3255	1000KCM	2632.14	1447.68	1316.07	

¹ Price Per 100 Ft.

XHHW-CROSS-LINKED POLYETHYLENE 90 DEGREE C DRY/75 DEGREE C WET - SOLID



Catalog Number	Item No	Description	Approx. Net Lbs. Per 1000 Ft.	Size	Per 1000 Ft.			
					Col. A	Col. B	Col. C	
14	23501	--	--	14	209.92	115.46	104.96	
12	23601	--	--	12	253.88	139.63	126.94	
10	23701	--	--	10	349.64	192.30	174.82	

XHHW-CROSS-LINKED POLYETHYLENE 90 DEGREE C DRY/75 DEGREE C WET - STRANDED

Catalog Number	Item No	Description	Approx. Net Lbs. Per 1000 Ft.	Size	Per 1000 Ft.			
					Col. A	Col. B	Col. C	
14	23801	--	18	14	234.16	128.79	117.08	
12	23901	--	26	12	294.44	161.94	147.22	
10	24001	--	40	10	420.28	231.15	210.14	
8	24051	--	66	8	690.72	379.90	345.36	
6	24101	--	100	6	971.20	534.16	485.60	
4	24151	--	150	4	1459.06	802.48	729.53	
3	24171	--	186	3	1746.62	960.64	873.31	
2	24181	--	231	2	2153.34	1184.34	1076.67	
1	24201	--	292	1	2741.24	1507.68	1370.62	
1/0	24226	--	363	1/0	2870.54	1578.80	1435.27	
2/0	24231	--	452	2/0	3595.02	1977.26	1797.51	
3/0	24236	--	565	3/0	4486.26	2467.44	2243.13	
4/0	24241	--	706	4/0	5548.44	3051.64	2774.22	
250KCM	24246	--	835	250KCM	6816.40	3749.02	3408.20	
300KCM	24251	--	995	300KCM	7855.82	4320.70	3927.91	