

# STANDARD NITRILE

## X3 Ultra™

### INDUSTRIAL GRADE NITRILE GLOVES



#### Recommended Uses



#### General Description

|                 |                  |                 |                |
|-----------------|------------------|-----------------|----------------|
| <b>Material</b> | Nitrile          | <b>Type</b>     | Non-Sterile    |
| <b>Color</b>    | Blue             | <b>Usage</b>    | Single Use     |
| <b>Shape</b>    | Ambidextrous     | <b>Interior</b> | Powder Free    |
| <b>Sizes</b>    | S - XL           | <b>Exterior</b> | Finger Texture |
| <b>Cuff</b>     | Beaded min. 0.04 | <b>Process</b>  | Chlorinated    |

#### Product Codes

|                |            |
|----------------|------------|
| <b>Small</b>   | XUNPF42100 |
| <b>Medium</b>  | XUNPF44100 |
| <b>Large</b>   | XUNPF46100 |
| <b>X-Large</b> | XUNPF48100 |

#### Packaging

|                  |                    |
|------------------|--------------------|
| <b>Box</b>       | 100 Gloves Per Box |
| <b>Box Dims</b>  | 224 x 124 x 55 mm  |
| <b>Case</b>      | 10 Boxes Per Case  |
| <b>Case Dims</b> | 285 x 258 x 235 mm |

#### Physical Properties

|                                |              |
|--------------------------------|--------------|
| <b>Tensile Strength</b>        | 14 Mpa (min) |
| <b>Tensile Strength (Aged)</b> | 14 Mpa (min) |
| <b>Powder Content</b>          | N/A          |
| <b>FDA Listing</b>             | N/A          |
| <b>Elongation</b>              | 500%         |
| <b>Elongation (Aged)</b>       | 400%         |
| <b>Protein Content</b>         | N/A          |
| <b>AQL Level</b>               | 4.0          |

#### Dimensions

|                  |             |                |             |
|------------------|-------------|----------------|-------------|
| <b>Weight</b>    | 3.0 ± 0.3 g | <b>Length</b>  | 230 mm      |
| <b>Thickness</b> |             | <b>Width</b>   |             |
| <b>Cuff</b>      | 1.5 mil     | <b>Small</b>   | 80 ± 10 mm  |
| <b>Palm</b>      | 2 mil       | <b>Medium</b>  | 95 ± 10 mm  |
| <b>Finger</b>    | 2 mil       | <b>Large</b>   | 110 ± 10 mm |
|                  |             | <b>X-Large</b> | 115 ± 10 mm |

#### Barcodes

