

### Combination of butyl and viton layer of 0.3mm for a maximum protection against hazardous chemicals

- The glove provides the best resistance to the most aggressive chemicals, without compromising dexterity or comfort.
- Flexible and excellent dexterity, designed for comfort with a natural, curved ergonomic shape and soft feel.



#### Industries

- Automotive
- Life Sciences
- Chemical

#### Applications

- Inspection, selecting, checking parts
- Loading and unloading of process equipment
- Handling incoming goods
- Transferring liquids and solids between vessels and tanks and process equipment
- Supervision of running operation
- Unexpected leakages spills or other releases

# AlphaTec®

ADVANCED CHEMICAL PROTECTION

## 38-612


Maximum protection from hazardous chemicals

### Key Features

- 38-612 viton/butyl offers protection against aliphatic, halogenated and aromatic hydrocarbons as well as concentrated mineral acids
- The glove is very flexible and provides excellent dexterity
- Designed for comfort with a natural, curved ergonomic shape and soft feel, offering easy donning and good grip



### Performance Standards



### Specifications

BRAND   STYLE	DESCRIPTION	SIZE	LENGTH	COLOR	PACKAGE
AlphaTec®38-612	Viton / Butyl Polymer,	8, 9, 10	300 mm, 12 Inches	Black	• 36 pairs in a carton, individually wrapped with insert

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 210  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### Canada

Ansell Canada Inc.  
105, rue Lauder  
Cowansville (Québec)  
J2K 2K8, Canada  
T: 1 800 363-8340  
F: 1 888 267-3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:  
[www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2019 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.