




Ventilated Storage Systems

Design Guide


An *easy guide* to
Storage Planning



Closet Design



Shelving & Hardware Selection




Installation

CLOSET DESIGNS

Adult Reach-in's - 4' to 6'

12" Linen and 12" SIR




ADULT REACH-IN 5' - Standard

4'	5'	6'

ARI05STD

12" SIR




ADULT REACH-IN 5' - Upgrade 1

4'	5'	6'

ARI05UP1

12" Open Slide®




ADULT REACH-IN 5' - Upgrade 2

4'	5'	6'

ARI05UP2

Adult Reach-in's - 7' to 10'

12" Linen and 12" SIR




ADULT REACH-IN 8' - Standard

7'	8'	9'	10'

ARI08STD

12" SIR




ADULT REACH-IN 8' - Upgrade 1

7'	8'	9'	10'

ARI08UP1

12" Open Slide® with Shoe Rack and 7-Runner Stor-Drawer System




ADULT REACH-IN 8' - Upgrade 2

7'	8'	9'	10'

ARI08UP2

Child Reach-in's - 4' to 8'

12" Linen and 12" SIR




CHILD REACH-IN 6' - Standard

4'	5'	6'	7'	8'

CRI06STD

12" Linen and 12" SIR




CHILD REACH-IN 6' - Upgrade 1

4'	5'	6'	7'	8'

CRI06UP1

12" Open Slide® and 12" Tight-Mesh with 7-Runner Stor-Drawer System



CHILD REACH-IN 6' - Upgrade 2


4'	5'	6'	7'	8'

CRI06UP2

CLOSET DESIGNS

Adult Walk-in's – 5' x 6', 6' x 6', 6' x 7'

12" Linen and 12" SIR




ADULT WALK-IN 6' x 6' - Standard

5' x 6'	6' x 6'	6' x 7'

AW06X065

12" Linen and 12" SIR with Shoe Rack




ADULT WALK-IN 6' x 6' - Upgrade 1

5' x 6'	6' x 6'	6' x 7'

AW06X061

12" Open Slide® with Shoe Rack and 10-Runner Stor-Drawer System




ADULT WALK-IN 6' x 6' - Upgrade 2

5' x 6'	6' x 6'	6' x 7'

AW06X062

Adult Walk-in's – 6' x 8', 6' x 9', 6' x 10'

12" Linen and 12" SIR




ADULT WALK-IN 6' x 8' - Standard

6' x 8'	6' x 9'	6' x 10'

AW06X085

12" Linen and 12" SIR with Shoe Rack




ADULT WALK-IN 6' x 8' - Upgrade 1

6' x 8'	6' x 9'	6' x 10'

AW06X081

12" Open Slide® with Shoe Rack and 10-Runner Stor-Drawer System




ADULT WALK-IN 6' x 8' - Upgrade 2

6' x 8'	6' x 9'	6' x 10'

AW06X082

Child Walk-in's – 5' x 5', 5' x 6', 6' x 6'

12" Linen and 12" SIR




CHILD WALK-IN 5' x 6' - Standard

5' x 5'	5' x 6'	6' x 6'

CW05X065

12" Linen and 12" SIR




CHILD WALK-IN 5' x 6' - Upgrade 1

5' x 5'	5' x 6'	6' x 6'

CW05X061

12" Tight-Mesh and 12" Open Slide® with 7-Runner Stor-Drawer System



CHILD WALK-IN 5' x 6' - Upgrade 2


5' x 5'	5' x 6'	6' x 6'

CW05X062

CLOSET DESIGNS

Pantry – 2' to 5'

16" Tight-Mesh




PANTRY 4' - Standard

2'	3'	4'	5'

PAN04STD

16" Tight-Mesh and 20" Tight Mesh




PANTRY 4' - Upgrade 1

2'	3'	4'	5'

PAN04UP1

16" Tight-Mesh and 20" Tight-Mesh with 7-Runner Stor-Drawer System




PANTRY 4' - Upgrade 2

2'	3'	4'	5'

PAN04UP2

Linen – 2' to 5'

16" Linen




LINEN 4' - Standard

2'	3'	4'	5'

LIN04STD

16" Linen and 20" Linen




LINEN 4' - Upgrade 1

2'	3'	4'	5'

LIN04UP1

16" Linen and 20" Linen with 7-Runner Stor-Drawer System




LINEN 4' - Upgrade 2

2'	3'	4'	5'

LIN04UP2

Laundry – 5' to 6'

12" Linen




LAUNDRY 6' - Standard

5'	6'

LAU06STD

12" Linen and 12" SIR




LAUNDRY 6' - Upgrade 1

5'	6'

LAU06UP1

16" Linen and 16" Open Slide®



LAUNDRY 6' - Upgrade 2


5'	6'

LAU06UP2

CLOSET DESIGNS

Laundry – 7' to 10'

12" Linen and 12" SIR




LAUNDRY 8' - Standard

7'	8'	9'	10'

LAU08STD

16" Linen and 16" SIR




LAUNDRY 8' - Upgrade 1

7'	8'	9'	10'

LAU08UP1

16" Tight-Mesh and 16" Open Slide® with 7-Runner Stor-Drawer System




LAUNDRY 8' - Upgrade 2

7'	8'	9'	10'

LAU08UP2

General Storage – 6' to 10'

12" Linen




GENERAL (STORAGE) 8' - Standard

6'	7'	8'	9'	10'

GEN08STD

16" Linen




GENERAL (STORAGE) 8' - Upgrade 1

6'	7'	8'	9'	10'

GEN08UP1

16" Tight-Mesh and 16" Linen




GENERAL (STORAGE) 8' - Upgrade 2


6'	7'	8'	9'	10'

GEN08UP2

SPACING GUIDELINES FOR CLOTHING AND GENERAL STORAGE

Numbers indicate how many items will fit PER FOOT of closet width when allowing 1-1/2" per hanger.

Double hang		per foot
	Suits/jackets	5
	Shirts/blouses	12
	Trousers/slacks	8
	Skirts	8

Single-hang		per foot
	Trousers hung by cuff	8
	Dresses	8
	Outer coats	4
	Robes/loungewear	6


Shoe Shelves	
Women's	Multiply number of pairs by 7 inches, total, divide by 12 for total footage.
Men's	Multiply number of pairs by 9 inches, total, divide by 12 for total footage.

Stored Items

Allow 12" - 14" for each stack of stored garments.

INSTALLATION TYPES AND MEASUREMENT GUIDELINES


Installation Types



1 Open-End-to-Wall Using Support Brace (shown) requires:

Back Clips, Side Wall Bracket, Support Brace, End Caps, Tri-Loc® II Anchor


Using Support Pole requires: Back Clips, Side Wall Bracket, Support Pole & Clips, End Caps



2 Open-End-to-Open-End Using Support Brace (shown) requires:


Back Clips, Support Braces, End Caps, Tri-Loc® II Anchor

Using Support Pole requires: Back Clips, Support Poles & Clips, End Caps



3 Wall-to-Wall requires:

Back Clips, Side Wall Brackets, End Caps



4 Shoe Rack requires:

Back Clips, End Caps, Shoe Rack Supports (Shoe Rack Support snaps on inverted shelf to hold shelf at an angle.)

Basic Guidelines: Custom Designing Closet Shelving Systems.

Simple Single Hang



Single Hang




Simple Double Hang




Multiple Shelves

Storage/Linen 13" apart




Treating Corners


1 Corner Rounder



2 Square Corner with Corner Bracket



3 Square Corner with Spacing




SELECTING SHELVING


Hanging Shelves

These dual-duty shelves are ideal for clothes closets, laundry, anywhere hanging space is needed. The Open Slide® style allows uninterrupted hanger movement along the entire shelf width. Corner Rounders continue hanging space around corners.

SHELF WITH HANGING ROD (S/R)



12" Shelf with Hanging Rod
Depth: 12"
Product No. 1110-1212




16" Shelf with Hanging Rod
Depth: 16"
Product No. 1110-1612

OPEN SLIDE (OS)



12" Open Slide® Hanging Shelf
Depth: 12"
Product No. 1710-1212
16" 1710-1612



Open Slide® design allows uninterrupted hanger movement along the entire width of the shelf.

CORNER ROUNDER SHELVES

12" Corner Rounder Shelf



Product No. 1110-1219
For use with 12" Shelf with Hanging Rod

16" Corner Rounder Shelf



Product No. 1110-1619
For use with 16" Shelf with Hanging Rod

12" Open Slide® Corner Rounder Shelf




Product No. 1710-1219
For use with 12" Open Slide® Hanging Shelf


Storage Shelves

Versatile and economical Storage/Linen Shelving creates space-saving storage for home and commercial use. Tight-Mesh design keeps even the smallest items upright.

STANDARD STORAGE SHELVES (L)




12" and 16" Standard Storage Shelf
Depth: 12"
Product No. 1210-1212
16" 1210-1612




20" Standard Storage Shelf
Depth: 20"
Product No. 1210-2012

TIGHT-MESH STORAGE SHELVES (TM)



9", 12" and 16" Tight-Mesh Storage Shelf
Depth: 9"
Product No. 1510-0912
12" 1510-1212
16" 1510-1612




20" Tight-Mesh Storage Shelf
Depth: 20"
Product No. 1510-2012

SCHULTE HARDWARE:

All SCHULTE Shelving can be installed with components from three main groups of hardware.

1. Back Clip

To attach back of shelf to wall. 1-1/2" from ends and every 11". Also used as a hold down clip at open ends and above Support Braces.




Versa-Clip™
For all substrates.


3. Support Braces - Support Poles

To support front of shelf or as a center support. Recommended spacing: every 3'6". For heavy loads, every 2'.

Use Support Poles for added strength on multiple-shelf applications.




For 9", 12", 16", 20" shelves.



2. Side Wall Bracket

To support front of shelf at side walls. Features double anchor to support the heaviest loads.



Side Wall Bracket with Tri-Loc® II Anchor

Where It Goes


1. Versa-Clips™*

* Patented

2. Side Wall Bracket

3. Support Pole


3. Support Brace



MISCELLANEOUS HARDWARE


Corner Bracket
To join shelving at 90° corner.

See bottom of previous page for application.




End Caps
To cover cut rods or a finished look.

Double End Caps
To provide a finished appearance and prevents hangers from sliding off an open-end installation.



Shoe Rack Supports
To convert Shelf with Hanging Rod or Storage Shelves to a shoe rack.

Begin first shelf 6" to 11" then stack shelves every 8".



	# Feet Hanging Shelf (S/R or OS)	# Feet Storage/ Linen Shelf (L or TM)	Corner Rounders (requires joiner hardware)	A Back Clips	B Side Wall Brackets	H, I Support Braces (requires anchors D)	J Support Poles (requires clips F)	C End Caps Large/ Small Double	L Shoe Rack Supports	Stor-Drawer Kits
5' Adult Reach-In										
Standard	5 (12R)	5 (12L)	—	12	4	2 (12")	—	6/10	—	—
Upgrade 1	10 (12R)	—	—	14	4	3 (12")	—	8/12/2	—	—
Upgrade 2	10 (OS)	—	—	14	4	—	1	8/12/2	—	—
8' Adult Reach-In										
Standard	8 (12R)	8 (12L)	—	20	4	4 (12")	—	6/10	—	—
Upgrade 1	18 (12R)	4 (12L)	—	29	4	3 (12")	—	12/24/2	—	—
Upgrade 2	18 (12OS)	4 (12L)	—	29	4	2	2	12/24/2	—	1-7R
6' Child Reach-In										
Standard	12 (12R)	6 (12L)	—	24	6	3 (12")	—	10/14	—	—
Upgrade 1	12 (12R)	10 (12L)	—	30	8	3 (12")	1	14/26	—	—
Upgrade 2	12 (12OS)	8 (12TM)	—	30	7	3 (12")	1	20/26	—	1-7R
5' x 6' Adult Walk-In										
Standard	22 (12R)	8 (12L)	—	40	6	18 (12")	—	20/44/4	—	—
Upgrade 1	22 (12R)	14 (12L)	—	48	6	10 (12")	2	24/50/4	3	—
Upgrade 2	22 (12OS)	14 (12TM)	—	49	6	10 (12")	2	40/62/4	12	1-10R
6' x 8' Adult Walk-In										
Standard	28 (12R)	h (12L)	—	54	6	18 (12")	—	20/44/4	—	—
Upgrade 1	36 (12R)	15 (12L)	—	70	8	12 (12")	2	26/48/4	4	—
Upgrade 2	23 (12OS)	19 (12TM)	2	60	4	10 (12") 4 (J)	2	44/62/2	12	1-10R
5' x 6' Child Walk-In										
Standard	25 (12R)	14 (12L)	—	44	12	19 (12")	—	22/42/4	—	—
Upgrade 1	20 (12R)	24 (12L)	—	57	12	10 (12")	2	48/64	—	—
Upgrade 2	10 (12OS)	14 (12TM)	2	54	10	8 (12") 4 (J)	2	38/50	—	1-7R
4' Pantry										
Standard	—	16 (16TM)	—	20	8	4 (16")	—	16/24	—	—
Upgrade 1	—	8 (16TM) 12 (20TM)	—	25	10	2 (16") 3 (20")	—	20/30	—	—
Upgrade 2	—	4 (12TM) 12 (16TM)	—	20	10	2 (16") 4 (20")	—	24/34	—	1-7R
4' Linen										
Standard	—	16 (16L)	—	20	8	4 (16")	—	8/24	—	—
Upgrade 1	—	8 (16L) 12 (20L)	—	25	10	2 (16") 3 (20")	—	12/32	—	—
Upgrade 2	—	8 (16L) 8 (20L)	—	20	8	2 (16") 2 (20")	—	16/34	—	2-7-R
6' Laundry										
Standard	—	6 (12L)	—	8	2	1 (12")	—	2/6	—	—
Upgrade 1	6 (12R)	6 (12L)	—	16	4	2 (12")	—	6/10	—	—
Upgrade 2	6 (16OS)	6 (16L)	—	16	4	1 (12") 1 (16")	—	8/14	—	—
8' Laundry										
Standard	8 (12R)	8 (12L)	—	20	4	4 (12")	—	2/10/2	—	—
Upgrade 1	8 (16R)	8 (16L)	—	20	4	2 (12")	—	8/12	—	—
Upgrade 2	8 (16OS)	8 (16TM)	—	20	4	2 (16")	—	8/12	—	1-7R
8' General Storage										
Standard	—	24 (12L)	—	36	—	12 (12")	—	6/18	—	—
Upgrade 1	—	32 (16L)	—	50	—	—	4	10/30	—	—
Upgrade 2	—	11 (16TM) 32 (16L)	—	56	—	—	4	16/36	—	—

S/R - Shelf with Hanging Rod
OS - Open Slide® Hanging Shelf
L - Standard Storage/Linen Shelf
TM - Tight-Mesh Storage Shelf
J - Joiner Support Brace

NOTE: Above hardware requirements will provide a guideline for your closet installations. Give actual closet dimensions to your dealer for precise requirements.

* Patented



5010-6814-40
Printed in U.S.A.