



SPECIFICATION SHEET

33-G115



SEAMLESS KNIT POLYESTER GLOVE WITH POLYURETHANE COATING

- Seamless knit nylon for great dexterity
- Polyurethane coated palm and fingers for abrasion resistance
- Breathable back for comfort
- Pair packed for ease of distribution

APPLICATIONS

- Electronic and computer assembly
- Quality control
- Inspection
- General assembly

CARE INSTRUCTIONS

Recommend washing gloves in slightly warm water not exceeding 40°C. A mild non-ionic detergent should be used. A 5-10 minute cycle time should be employed. Tumble dry on low - maximum temperature 140°F (60°C).

TECHNICAL DATA

MATERIAL	Polyester with polyurethane coating on palm and fingers					
CONSTRUCTION	Seamless Knit					
COLOR	Shell: ■ Gray / Coating: ■ Gray					
SIZES	XS - XXL					
PACKAGING	1 pair per bag, 12 pairs per dozen, 25 dozen per case					
CASE DIMENSIONS	24.8" x 11.0" x 18.1" / 63cm x 28cm x 46cm					
CASE WEIGHT	XS	S	M	L	XL	XXL
	14.2 lbs 6.4 kg	15.6 lbs 7.1 kg	16 lbs 7.3 kg	17 lbs 7.7 kg	18 lbs 8.2 kg	19.1 lbs 8.7 kg
COO	China					



PERFORMANCE PROPERTIES

EN388: 3121 ASTM F2992-15 ANSI Cut Level A4 (Adopted by ANSI/ISEA 02/16)


ABRASION	0	1	2	3	4	-
CUT	0	1	2	3	4	5
TEAR	0	1	2	3	4	-
PUNCTURE	0	1	2	3	4	-

BARCODES

ITEM	BAG	DOZEN	CASE
■ 33-G115/XS	---	01616314124876	02616314124875
■ 33-G115/S	---	01616314124852	02616314124851
■ 33-G115/M	---	01616314124845	02616314124844
■ 33-G115/L	---	01616314124838	02616314124837
■ 33-G115/XL	---	01616314124869	02616314124868
■ 33-G115/XXL	---	01616314124883	02616314124882

DIMENSIONS (in/cm)

	XS	S	M	L	XL	XXL
A	8.46 / 21.5	9 / 23	9.4 / 24	9.8 / 25	10.2 / 26	10.6 / 27
B	3.5 / 9	3.6 / 9.2	3.7 / 9.5	3.8 / 9.8	4 / 10.2	4.3 / 11
H	■ Purple	■ Red	■ Yellow	■ Brown	■ Black	■ Blue



PROTECTIVE INDUSTRIAL PRODUCTS, INC. | BRINGING THE BEST OF THE WORLD TO YOU®

AMERICAS: (800) 262-5755 • (518) 861-0133 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobal.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED.