

 (7.1) KMJ Adapters

KMJ Adapters

OCC's Keystone adapters offer a full array of data, video, and audio ports for fiber, copper, coaxial and speaker cables. Featuring snap-in accessibility and a wide arrange of multimedia options, the OCC KMJ adapter line gives customers a flexible solution to meet any connectivity demand.

- Fits all OCC Keystone faceplates and surface-mount boxes



AKSVHS12



AKBLK12



AKBP212



AKRCA110B12



AKF12



AKRCA110Y12



AKDLCM00



AKSCM01



AKRCAP12



AKSTM12

KMJ Adapters

CATALOG NUMBER	DESCRIPTION
AKSCMxx	KMJ snap-in SC multimode adapter
AKSTMxx	KMJ snap-in ST multimode adapter
AKDLCMxx	KMJ snap-in dual LC multimode adapter
AKBNCxx	KMJ snap-in BNC coupler
AKFxx	KMJ snap-in F coupler
AKSVHSxx	KMJ snap-in Super VHS adapter
AKRCAPxx	KMJ snap-in gold-plated RCA bulkhead adapter
AKRCA110yxx	KMJ snap-in RCA to 110 adapter
AKBP2xx	KMJ snap-in gold-plated binding posts (pair)
AKBC2xx	KMJ snap-in gold-plated banana adapters (pair)
AKBLKxx	KMJ snap-in blank adapters

Replace "xx" with color choice: **00** = electrical ivory, **01** = office white, or **12** = bright white.
 Replace "y" with color inset choice: **R** = red, **Y** = yellow, **B** = black, or **W** = white.

KMJ Keyed LC Adapters

CATALOG NUMBER	DESCRIPTION
LAXAKDLCKWTxx	Limited Access keystone adapter, DLC, keyed, SM/MM, white
LAXAKDLCKORxx	Limited Access keystone adapter, DLC, keyed, SM/MM, orange
LAXAKDLCKPLxx	Limited Access keystone adapter, DLC, keyed, SM/MM, purple
LAXAKDLCKSLxx	Limited Access keystone adapter, DLC, keyed, SM/MM, slate
LAXAKDLCKBNxx	Limited Access keystone adapter, DLC, keyed, SM/MM, brown
LAXAKDLCKAQxx	Limited Access keystone adapter, DLC, keyed, SM/MM, aqua
LAXAKDLCKRSxx	Limited Access keystone adapter, DLC, keyed, SM/MM, rose
LAXAKDLCKGNxx	Limited Access keystone adapter, DLC, keyed, SM/MM, green
LAXAKDLCKRDxx	Limited Access keystone adapter, DLC, keyed, SM/MM, red
LAXAKDLCKYLxx	Limited Access keystone adapter, DLC, keyed, SM/MM, yellow
LAXAKDLCKPKxx	Limited Access keystone adapter, DLC, keyed, SM/MM, pink

Replace "xx" with color choice: **00** = electrical ivory, **01** = office white, or **12** = bright white.

(7.2) UMJ Adapters

UMJ Adapters

For multimedia options, OCC created a complete line of data, video, and audio ports for fiber, copper, coaxial and speaker cables. Combined with the multicolor, low-profile recessed bezels, OCC's UMJ-style adapters offer a flexible alternative for port identification, no matter what the application.

- Available with 12 color options
- Secure mounting locks adapters into faceplate
- Fits all OCC UMJ faceplates and surface-mount boxes



UMJ Adapters

CATALOG NUMBER	DESCRIPTION
AASCMxx	UMJ snap-in SC multimode adapter
AASCSxx	UMJ snap-in SC single-mode adapter
AASTMxx	UMJ snap-in ST multimode adapter
AASTSxx	UMJ snap-in ST single-mode adapter
AADLCMxx	UMJ snap-in dual LC multimode adapter
AAFxx	UMJ snap-in F coupler
AABNCxx	UMJ snap-in BNC coupler
AARCAxx	UMJ snap-in RCA adapter with solder tab
APBLKxx	UMJ snap-in blank bezel (20 pack)

Replace "xx" with color code.

"XX" COLOR CODES		
00 – Electrical Ivory	05 – Blue	10 – Purple
01 – Office White	06 – Data Gray	11 – Brown
02 – Black	07 – White	12 – Bright White
03 – Red	08 – Orange	
04 – Green	09 – Yellow	

UMJ Keyed LC Adapters

CATALOG NUMBER	DESCRIPTION
LAXAAKDLCGNxx	Limited Access adapter, DLC, keyed, SM/MM, green
LAXAAKDLCRDxx	Limited Access adapter, DLC, keyed, SM/MM, red
LAXAAKDLCLYxx	Limited Access adapter, DLC, keyed, SM/MM, yellow
LAXAAKDLCPKxx	Limited Access adapter, DLC, keyed, SM/MM, pink
LAXAAKDLCTxx	Limited Access adapter, DLC, keyed, SM/MM, white
LAXAAKDLCORxx	Limited Access adapter, DLC, keyed, SM/MM, orange
LAXAAKDLCPxx	Limited Access adapter, DLC, keyed, SM/MM, purple
LAXAAKDLCSxx	Limited Access adapter, DLC, keyed, SM/MM, slate
LAXAAKDLCBNxx	Limited Access adapter, DLC, keyed, SM/MM, brown
LAXAAKDLCAQxx	Limited Access adapter, DLC, keyed, SM/MM, aqua
LAXAAKDLCSxx	Limited Access adapter, DLC, keyed, SM/MM, rose

Replace "xx" with color choice: **00** = electrical ivory, **01** = office white, or **12** = bright white.

 (9.4) Cable Management

Horizontal Cable Management

Optimize closet space and organize your cabling system with any of OCC's horizontal cable managers. This complete line of horizontal cable management provides a versatile selection for maintaining cable runs and preserving connectivity components' lifespan.

Ring and Velcro Horizontal Cable Management


CATALOG NUMBER	DESCRIPTION
CM102	19" cable management panel, 1RU, Velcro® belts
CM104	Front/rear side towel bar, 1RU
CM105	Cable management tab, Velcro® belts




CM102

Horizontal Cable Organizers

CATALOG NUMBER	DESCRIPTION
CO17519	19" front-side cable organizer, intra-bay, 1.75", 1RU
CO17519L	19" front-side cable organizer, inter-bay, 1.75", 1RU
CO1719H	19" front-side cable organizer, inter-bay, 1.75", 1RU high density
CO3519	19" front-side cable organizer, intra-bay, 3.5", 2RU
CO3519L	19" front-side cable organizer, inter-bay, 3.5", 2RU
COMB3519	19" cable organizer, single-sided with cover, 3.5", 2RU
COMBD3519	19" cable organizer, double-sided with cover, 3.5", 2RU
CMB19	19" cable management bar for Cat 5e panel
SB1719	19" cable support bar kit for EIA mounting



CO3519



CO17519

Finger Duct Horizontal Cable Organizers

CATALOG NUMBER	DESCRIPTION
CM401	19" horizontal cable manager, finger style, 1RU single-sided
CM402	19" horizontal cable manager, finger style, 1RU double-sided
CM403	19" horizontal cable manager, finger style, 2RU single-sided
CM404	19" horizontal cable manager, finger style, 2RU double-sided

