

BBP®33 Wire & Cable Materials:

B-498 Repositionable Vinyl Cloth Material

A strong holding label can be removed cleanly and reapplied

- vinyl cloth label for marking wires, cables and inside-panel components that
- Highly unique adhesive and cloth construction gives excellent holding power and still allows for clean removal and reapplication
- Ideal choice for marking both ends of a wire that you may need to cut shorter before final termination





Figure 1



Service temp: -40°F to 175°F

Agency Approvals:

Fits Printer Model	Diagram	Catalog #	B#	Material	Color	Label Width A Inch (mm)	Label Height B Inch (mm)	Horiz. Repeat C Inch (mm)	Vert. Repeat D Inch (mm)	Web Width E Inch (mm)	Labels Per Row	Labels Per Roll	Rec. Ribbon
BBP33	Fig. 1	B33-90-498	B-498	Vinyl Cloth	White	0.250 (6.4)	1.437 (36.5)	0.350 (8.9)	1.562 (39.7)	2.200 (55.9)	6	2500	B30-R6200
BBP33	Fig. 1	B33-68-498	B-498	Vinyl Cloth	White	0.500 (12.7)	0.750 (19.1)	0.600 (15.2)	0.875 (22.2)	2.500 (63.5)	4	5000	B30-R6200
BBP33	Fig. 1	B33-87-498	B-498	Vinyl Cloth	White	0.500 (12.7)	1.437 (36.5)	0.600 (15.2)	1.562 (39.7)	3.700 (94)	6	2500	B30-R6200
BBP33	Fig. 1	B33-14-498	B-498	Vinyl Cloth	White	0.650 (16.5)	0.200 (5.1)	0.700 (17.8)	0.300 (7.6)	2.950 (74.9)	4	5000	B30-R6200
BBP33	Fig. 1	B33-1-498	B-498	Vinyl Cloth	White	0.750 (19.1)	0.250 (6.4)	0.800 (20.3)	0.350 (8.9)	3.350 (85.1)	4	5000	B30-R6200
BBP33	Fig. 1	B33-91-498	B-498	Vinyl Cloth	White	0.750 (19.1)	0.937 (23.8)	0.850 (21.6)	1.062 (27.0)	3.500 (88.9)	4	2500	B30-R6200
BBP33	Fig. 1	B33-165-498	B-498	Vinyl Cloth	White	0.800 (20.3)	1.437 (36.5)	0.900 (22.9)	1.562 (39.7)	3.700 (94.0)	4	2500	B30-R6200
BBP33	Fig. 1	B33-95-498	B-498	Vinyl Cloth	White	0.800 (20.3)	1.437 (36.5)	0.900 (22.9)	1.562 (39.7)	2.800 (71.1)	3	2500	B30-R6200
BBP33	Fig. 1	B33-5-498	B-498	Vinyl Cloth	White	1.000 (25.4)	0.500 (12.7)	1.075 (27.3)	0.600 (15.2)	3.350 (85.1)	3	5000	B30-R6200
BBP33	Fig. 1	B33-88-498	B-498	Vinyl Cloth	White	1.000 (25.4)	0.750 (19.1)	1.100 (27.9)	0.875 (22.2)	2.300 (58.4)	2	2500	B30-R6200
BBP33	Fig. 1	B33-89-498	B-498	Vinyl Cloth	White	1.000 (25.4)	1.437 (36.5)	1.100 (27.9)	1.562 (39.7)	3.400 (86.4)	3	2500	B30-R6200

BBP®33 Wire & Cable Materials:

B-498 Adhesive Terminal Block Material

Holds strong but can be removed cleanly & reapplied.

- Specially designed narrow-width continuous label for alignment on terminal blocks and patch panels
- Highly unique adhesive and vinyl cloth construction gives excellent holding power and still allows for clean removal and reapplication




Figure 3



Service temp: -40°F to 175°F

Agency Approvals:

Fits Printer Model	Diagram	Catalog #	B#	Material	Color	Label Width A Inch (mm)	Roll Length B Inch (mm)	Web Width E Inch (mm)	Labels Per Roll	Rec. Ribbon
BBP33	Fig. 3	B33C-240-498	B-498	Vinyl Cloth	White	0.240 (6.1)	85 ft. (25.9m)	1.000 (25.4)	1 roll (cont.)	B30-R6200
BBP33	Fig. 3	B33C-312-498	B-498	Vinyl Cloth	White	0.312 (7.9)	85 ft. (25.9m)	1.000 (25.4)	1 roll (cont.)	B30-R6200
BBP33	Fig. 3	B33C-375-498	B-498	Vinyl Cloth	White	0.375 (9.5)	85 ft. (25.9m)	1.000 (25.4)	1 roll (cont.)	B30-R6200



Did You Know? www.BradyID.com

Visit BradyID.com for online ordering and instant access to:

- Product Info
- Product Demos
- Custom Orders
- Whitepapers
- Webinars
- And More!

