

# IDXPERT™ Handheld Labeler

www.BradyID.com/idxpert

Portable Label Printers



**View Online!**

Visit [www.BradyID.com/idxpert](http://www.BradyID.com/idxpert) or scan this code for more information or to view a demo video of the IDXPERT Labeler.



### Your Complete Printing Solution:

IDXPERT cartridges with material and print ribbon .....Page 22

Brady's IDXPERT™ Handheld Labeler is the ideal tool for affordable, on-the-spot labeling in datacomm, electrical, and industrial workplaces. This 300 dpi thermal transfer label printing creates die-cut labels, self-laminating labels, sleeves and continuous tape labels.

### Three Versions Available:

1. "Qwerty" keyboard layout style for fast typing
2. "ABC" handheld style for maximum portability
3. "Continuous Only" version only prints on continuous lengths of material

Catalog #	Description
XPERT-ABC	Printer* - ABC Layout
XPERT-KEY	Printer* - KEYBOARD Layout
XPERT-CONT	Printer* - Continuous Printing Only
XPERT-HC-ABC	Hard Case for ABC Layout
XPERT-HC-KEY	Hard Case for KEYBOARD Layout
XPERT-AC	AC Adapter
LABXPERT-SER-USB	Serial-to-USB adapter for PC cable
PCCABLE-1	Spare PC Cable for Upgrades Only
PCK-5	Cleaning Kit
LM5STDE	LabelMark™5 Software (single user)
XPERT-ABC-KIT-LM	Printer* ABC Layout, AC Power Supply and LabelMark™5 Standard Software
XPERT-KEY-KIT-LM	Printer* Keyboard Layout, AC Power Supply and LabelMark™5 Standard Software

*\*Printer purchase included Hard Case, 1.5" Continuous Sample Roll Tape, PC cable, Product CD and 1 year Limited Warranty.*



### More Types of Labels

- Colored continuous tapes for lean, equipment and safety identification
- PermaSleeve® wire marker sleeves
- Self-laminating wire & cable markers
- Terminal block, patch panel, faceplate & outlet markers
- General-purpose industrial die-cut labels

### More Sizes

- Prints from .06" up to 1.25" characters on label stock up to 1.5" wide

### More Symbols

- Code 39 and 128 barcodes
- 82 symbols including electrical, voice/data, safety & protection, warning, and machine & operational

### More Brains

- Drop Lock & Go™ Smart Cartridges™ are fast to install and remove
- Electronically pre-calibrated to orient the label the way you need it with no special keys to press
- Print stand-alone or from a PC (with optional Brady LabelMark™ software)
- Memory to store frequently used set-ups

### Prints Clean & Fast

- Fast print speed, plus non-smearing thermal transfer print quality.
- Flexible text editing capabilities

### Less Waste

- Edge-to-edge printing on continuous tapes so you don't pay for unused label material
- Die-cut labels are pre-cut to the size you need


## Let the IDXPERT portable printer work for you.



Voice & Data Communications



PermaSleeve® Wire Marking Sleeves



Terminal Blocks



Self-Laminating Labels



Patch Panel & Faceplates



General ID ...and many more!