


Straight Blade Devices TradeMaster® Receptacles


2 Pole, 3 Wire Grounded 15A, 125V




3232 Series



3232-S Series





3232-MH Series



880 Series

Features

- High-impact resistant thermoplastic construction.
- Extra-long strap.
- Quickloop wire looping aid.
- Long-term blade retention.
- Combination head screws.
- Extra-large circuit break-off tabs.
- Side-access speed wire release.
- Ultrasonic welding of face to back body.
- Side wire #12 - #14 AWG, speed wire #14 AWG only.
- "S" model provides automatic ground clip.

| Catalog Number | Rating A. V. | Color | NEMA Config. No. | 3rd Party Compliance | |
|---|-----------------|--------------|---------------------|---|---|
| | | | |  UL498 |  C22.2 42M |
| Duplex Receptacle | | | | | |
| 3232-I | 15 125 | Ivory | 5-15R | • | |
| 3232-W | 15 125 | White | 5-15R | • | |
| 3232 | 15 125 | Brown | 5-15R | • | |
| 3232-LA | 15 125 | Light Almond | 5-15R | • | |
| 🇨🇦 3232-ICN | 15 125 | Ivory | 5-15R | • | • |
| 🇨🇦 3232-WCN | 15 125 | White | 5-15R | • | • |
| Self-Grounding | | | | | |
| 3232-SI | 15 125 | Ivory | 5-15R | • | |
| 3232-SW | 15 125 | White | 5-15R | • | |
| 3232-S | 15 125 | Brown | 5-15R | • | |
| 4-Terminal, Screws In | | | | | |
| 3232-I4 | 15 125 | Ivory | 5-15R | • | |
| 3232-W4 | 15 125 | White | 5-15R | • | |
| 3232-4 | 15 125 | Brown | 5-15R | • | |
| Duplex Receptacle - Without Ears | | | | | |
| 3232-IMH | 15 125 | Ivory | 5-15R | • | |
| 3232-WMH | 15 125 | White | 5-15R | • | |
| 3232-MH | 15 125 | Brown | 5-15R | • | |
| 8-Hole Speed Wire - Without Terminal Screws | | | | | |
| 880-I | 15 125 | Ivory | 5-15R | • | |
| 880-W | 15 125 | White | 5-15R | • | |
| 880 | 15 125 | Brown | 5-15R | • | |
| 8-Hole Speed Wire - Without Ears - Without Terminal Screws | | | | | |
| 880-IMH | 15 125 | Ivory | 5-15R | • | |
| 880-WMH | 15 125 | White | 5-15R | • | |
| 880-MH | 15 125 | Brown | 5-15R | • | |

🇨🇦 Denotes Canadian catalog number. All Canadian products have Combination Slotted/Robertson Head Brass Screws.



NEMA
5-15R

All devices listed on this page conform to NEMA WD-1.