

**HUBBELL**  
**Advantage**

- Premium Quality High Performance Components
- Quick and Easy Snap-in Design to Fit any Suitable FCR, FPR, FCW or FTU Series Enclosures
- CSI Specifications and Drawings Available
- Wide Range of Adapter Types and High Density Options for Space Savings

**Specifications**


- Material: 16ga cold rolled steel
- Finish: durable black powder coat
- Dimensions: 1.1" W X 5.1" H
- SM/MM insertion loss: <0.50dB (0.25dB typical)
- Operating temperature: 0 °C to +75 °C

**Standards/Listings/Verifications**

- TIA-568-C.3
- TIA-604-FOCIS


**LC Duplex**

Description	Phosphor Bronze Multimode Only	Zirconia Ceramic Singlemode/Multimode
LC 6-port (3 LC duplex)	<b>FSPLCDM3xx</b>	<b>FSPLCDS3xx</b>
LC 12-port (6 LC duplex)	<b>FSPLCDM6xx</b>	<b>FSPLCDS6xx</b>
LC 24-port (12 LC duplex)	<b>FSPLCDM12xx</b>	<b>FSPLCDS12xx</b>




**LC Quad**

Description	Phosphor Bronze Multimode Only	Zirconia Ceramic Singlemode/Multimode
LC 12-port (3 LC quad)	<b>FSPLCQM3xx</b>	<b>FSPLCQS3xx</b>
LC 16-port (4 LC quad)	<b>FSPLCQM6xx</b>	<b>FSPLCQS6xx</b>
LC 24-port (6 LC quad)	<b>FSPLCQM12xx</b>	<b>FSPLCQS12xx</b>



**SC Duplex, FSP Adapter Panels**

Description	Phosphor Bronze Multimode Only	Zirconia Ceramic Singlemode/Multimode
SC 6-port (3 SC duplex)	<b>FSPSCDM3xx</b>	<b>FSPSCDS3xx</b>
SC 8-port (4 SC duplex)	<b>FSPSCDM4xx</b>	<b>FSPSCDS4xx</b>
SC 12-port (6 SC duplex)	<b>FSPSCDM6xx</b>	<b>FSPSCDS6xx</b>



xx = Color: **AQ** (Aqua), **BE** (Beige), **BK** (Black), **B** (Blue), **GN** (Green), **OR** (Orange), **R** (Red), and **Y** (Yellow).

**SC to ST-Style Duplex**

Description	Phosphor Bronze Sleeves	Zirconia Ceramic Sleeves
ST-SC 6-port, blue	<b>FSPSCST3</b>	<b>FSPSCSTD3</b>
ST-SC 12-port, blue	<b>FSPSCST6</b>	<b>FSPSCSTD6</b>



**ST-Style Duplex**

Description	Phosphor Bronze Sleeves	Zirconia Ceramic Sleeves
ST duplex, 6-port, blue	<b>FSPSTD3</b>	<b>FSPSTD3</b>
ST duplex, 12-port, blue	<b>FSPSTD6</b>	<b>FSPSTD6</b>



## FC Simplex

Description	Color	Zirconia Ceramic Sleeves
FC 6-port (6 FC)	Nickel Plate	<b>FSPFC6</b>
FC 8-port (8 FC)	Nickel Plate	<b>FSPFCSS8</b>



FSPFC6

## ST-Style Simplex

Description	Color	Phosphor Bronze Sleeves	Zirconia Ceramic Sleeves
ST-style 6-port		<b>FSPST6</b>	<b>FSPSTSS6</b>
ST-style 8-port		<b>FSPST8</b>	<b>FSPSTSS8</b>



FSPST6

## SC Simplex, APC

Description	Color	Zirconia Ceramic Sleeves
SC 6-port (6 SC)	Green	<b>FSPSCA6</b>
SC 8-port (8 SC)	Green	<b>FSPSCA8</b>



FSPSCA6

## SC Simplex

Description	Color	Phosphor Bronze Sleeves	Zirconia Ceramic Sleeves
SC 6-port (6 SC)	Blue	<b>FSPSC6</b>	<b>FSPSCSS6</b>
SC 8-port (8 SC)	Blue	<b>FSPSC8</b>	<b>FSPSCSS8</b>
SC 12-port (12 SC)	Blue	<b>FSPSC12</b>	<b>FSPSCSS12</b>



FSPSC6

## MT-RJ

Description	Color	Catalog No.
MT-RJ 6-port	Black	<b>FSPMTRJ6</b>
MT-RJ 8-port	Black	<b>FSPMTRJ8</b>



FSPMTRJ8

## JACK-PACK®, Unloaded

Description	Catalog No.
Keystone 4-port	<b>FSPHD4X</b>
Keystone 6-port	<b>FSPHD6X*</b>

\*Will not fit into FTU2 series, FTU4SP or FCR2U9SP enclosures.



FSPHD4X

## MTP

Description	Catalog No.
MTP simplex 6-port (72 fiber)	<b>FSPMTPxx6</b>
MTP duplex 8-port (96 fiber)	<b>FSPMTPDxx4</b>
MTP duplex 12-port (144 fiber)	<b>FSPMTPDxx6</b>

xx = Color: **AQ** (Aqua), **BE** (Beige), **BK** (Black), and **B** (Blue).



FSPMTPAQ6

## FSP Adapter Panel, Blank

Description	Catalog No.
FSP panel blank, snap-in	<b>FSPB</b>



FSPB

## FSP Adapter Panels, Unloaded

Description	Catalog No.
6 SC simplex or LC duplex	<b>FSPSC6X</b>
8 SC simplex or LC duplex	<b>FSPSC8X</b>
12 SC simplex or LC duplex	<b>FSPSC12X</b>
3 SC duplex or LC quad	<b>FSPSCD3X</b>
4 SC duplex or LC quad	<b>FSPSCD4X</b>
6 SC duplex or LC quad	<b>FSPSCD6X</b>
6 ST-style	<b>FSPST6X</b>
8 ST-style	<b>FSPST8X</b>



FSPSC6X



FSPSC8X



FSPSCD3X



FSPSCD6X