

PASS & SEYMOUR®

DIMMERS

# Install a new level of simplicity



designed to be better.™

 **legrand**®

# Harmony® Dimmers



## \*\*COLOR DESIGNATION

<b>W</b>	White
<b>LA</b>	Light Almond
<b>I</b>	Ivory
<b>BK</b>	Black
<b>-</b>	Brown
<b>GRY</b>	Gray
<b>NI</b>	Nickel
<b>AB</b>	Antique Brass
<b>DB</b>	Dark Bronze



PART NO.	DESCRIPTION	COLOR	RATING
H703PTUTC*	<b>Tru-Universal™</b> Single Pole/3-Way, Preset	Three Interchangeable Face Colors: Ivory, White, Light Almond	120V Incandescent, Halogen & ELV: 700W, MLV: 500VA, CFL/LED: 450W, EFL: 5.5A
H703PTUW		White	
HCL453PTC*	<b>CFL/LED</b> Single Pole/3-Way, Preset	Three Interchangeable Face Colors: Ivory, White, Light Almond	120V, 450W CFL/LED; 700W Incandescent
HCL453PW		White	
HFB83PTC	<b>Fluorescent</b> Single Pole/3-Way, Preset	Three Interchangeable Face Colors: Ivory, White, Light Almond	120V, 8A
HFB83PW		White	
H4FBL3PTC	<b>Fluorescent</b> Single Pole/3-Way, Preset <i>Available June 2015</i>	Three Interchangeable Face Colors: Ivory, White, Light Almond	0-10V
H4FBL3PW		White	
HLV703PTC	<b>Magnetic Low Voltage</b> Single Pole/3-Way, Preset	Three Interchangeable Face Colors: Ivory, White, Light Almond	120V, 700VA
HLV703PW		White	
HLV1103PTC	<b>Magnetic Low Voltage</b> Single Pole/3-Way, Preset	Three Interchangeable Face Colors: Ivory, White, Light Almond	120V, 1100VA
HLV1103PW		White	
H703PTC	<b>Incandescent</b> Single Pole/3-Way, Preset	Three Interchangeable Face Colors: Ivory, White, Light Almond	120V, 700W
H703P**CCV4		White, Antique Brass, Dark Bronze, Nickel	
H1103PTC*		Three Interchangeable Face Colors: Ivory, White, Light Almond	
H1103PW		White	120V, 1100W
HDH163PTC*	<b>Fan Speed Control</b> De-hummer, Single Pole/3-Way	Three Interchangeable Face Colors: Ivory, White, Light Almond	120V, 1.6A
HDH163PW*		White	
H703PMMTUTC	<b>Tru-Universal Multi-Location Master Dimmer</b> Single Pole/3-Way, Preset <i>Available Fall 2015</i>	Three Interchangeable Face Colors: Ivory, White, Light Almond	120V Incandescent, Halogen & ELV: 700W, MLV: 500VA, CFL/LED: 450W, EFL: 5.5A
H703PMMTUW		White	
HCL453PMMTC*	<b>CFL/LED Multi-Location Master Dimmer</b> Single Pole/3-Way, Preset	Three Interchangeable Face Colors: Ivory, White, Light Almond	120V, 450W CFL/LED; 700W Incandescent
HCL453PMMW		White	
HDH163PMMTC	<b>Fan Speed Control Multi-Location Master</b> De-hummer, Single Pole/3-Way <i>Available Fall 2015</i>	Three Interchangeable Face Colors: Ivory, White, Light Almond	120V, 1.6A
HDH163PMMW		White	
HMRTC	<b>Multi-Location Remote</b> Single Pole/3-Way	Three Interchangeable Face Colors: Ivory, White, Light Almond	120V
HMRW		White	
PART NO.	DESCRIPTION	COLOR	
HKIT**	Interchangeable Face Plate	Ivory, White, Light Almond, Black, Brown, Gray, Nickel, Antique Brass, Dark Bronze	
HMKIT**	Multi-Location Dimmer Interchangeable Face Plate		
HDHKIT**	Multi-Location De-Hummer Fan Speed Control Interchangeable Face Plate		
HMRKIT**	Multi-Location Remote Dimmer Interchangeable Face Plate		

\*Available in VisionPak™ packaging, add "CCV6" to Catalog Number. Example: H703PTUTC6.

All devices are US LISTED.