

Threaded bodies for heavy wall rigid and IMC.  
Set screw bodies for thin wall conduit (EMT)

	Catalog No.	Catalog No.	Hub Size	
Through Feed	<b>Rigid/IMC</b>	<b>EMT</b>		
	AC-1	BC-1	1/2"	
	<b>AC-2</b>	BC-2	3/4"	
	AC-3	BC-3	1"	
	AC-4	BC-4	1 1/4"	
	AC-5	BC-5	1 1/2"	
	AC-6	BC-6	2"	
	•AC-7		2V	
	•AC-8		3"	
	•AC-9		3V	
	•AC-10		4"	
	<b>*D-PAK™</b>			
	†DAC-1-CG		1/2"	
	†DAC-2-CG		3/4"	
	†DAC-3-CG		1"	



	Catalog No.	Catalog No.	Hub Size	
Back-Opening	ALB-1	BLB-1	1/2"	
	ALB-2	BLB-2	V	
	ALB-3	BLB-3	1"	
	ALB-4	BLB-4	1 1/4"	
	ALB-5	BLB-5	1V	
	ALB-6	BLB-6	2"	
	•ALB-7	•BLB-7	2 1/2"	
	•ALB-8	•BLB-8	3"	
	•ALB-9	•BLB-9	3V	
	•ALB-10	•BLB-10	4"	
	<b>*D-PAK™</b>			
	†DALB-1-CG	◊DBLB-1-C	V	
	†DALB-2-CG	◊DBLB-2-C	3/4"	
	†DALB-3-CG	◊DBLB-3-C	1"	
	tDALB-4-CG		1V	
†DALB-5-CG		1V		
tDALB-6-CG		2"		

	Catalog No.	Catalog No.	Hub Size	
Left Side Opening	ALL-1	BLL-1	V	
	ALL-2	BLL-2	3/4"	
	ALL-3	BLL-3	1"	
	ALL-4		1V	
	ALL-5		1 1/2"	
	ALL-6		2"	
	•ALL-7		2V	
	•ALL-8		3"	
	•ALL-9		3V	
	•ALL-10		4"	
	<b>*D-PAK™</b>			
	†DALL-1-CG		1/2"	
	†DALL-2-CG		3/4"	
	†DALL-3-CG		1"	

	Catalog No.	Catalog No.	Hub Size	
Right Side Opening	ALR-1	BLR-1	1/2"	
	ALR-2	BLR-2	3/4"	
	ALR-3	BLR-3	1"	
	ALR-4		1V	
	ALR-5		1V	
	ALR-6		2"	
	•ALR-7		2V	
	•ALR-8		3"	
	•ALR-9		3V	
	•ALR-10		4"	
	<b>*D-PAK™</b>			
	†DALR-1-CG		1/2"	
	†DALR-2-CG		3/4"	
	†DALR-3-CG		1"	

• Shipped with one CV cover  
 ◊ Shipped with one SCV cover  
 † Shipped with one SCV cover and one GKN gasket  
 \* See Pages 22 - 23 for complete D-PAK assortment

- Retained stainless steel cover screws
- Cubic capacity UL and CSA clearly shown
- Smooth throats for easy wire pulling
- Ultra-high pressure die cast copper-free aluminum
- UL Listed, CSA Certified

	Catalog No.	Catalog No.	Hub Size
Dead End	AE-1		1/2"
	AE-2		3/4"


	Catalog No.	Catalog No.	Hub Size
Left/Right Side Opening	<b>Rigid/IMC</b>	<b>EMT</b>	
	◊ALRL-1	◊BLRL-1	1/2"
	◊ALRL-2	◊BLRL-2	3/4"
	◊ALRL-3	◊BLRL-3	1"
	◊ALRL-4	◊BLRL-4	1 1/4"
	◊ALRL-5	◊BLRL-5	1V
◊ALRL-6	◊BLRL-6	2"	

	Catalog No.	Catalog No.	Hub Size	
T-Style	AT-1	BT-1	V	
	AT-2	BT-2	3/4"	
	AT-3	BT-3	1"	
	AT-4	BT-4	1 1/4"	
	AT-5	BT-5	1 1/2"	
	AT-6	BT-6	2"	
	•AT-7		2 1/2"	
	•AT-8		3"	
	•AT-9		3 1/2"	
	•AT-10		4"	
	<b>*D-PAK™</b>			
	†DAT-1-CG		V	
	†DAT-2-CG		3/4"	
	†DAT-3-CG		1"	

## COVERS AND GASKETS

For Threaded and Set Screw Conduit Bodies

	Catalog No.	Catalog No.	Fits Hub Size
Covers	<b>Die Cast</b>	<b>Stamped</b>	
	CV-1	SCV-1	1/2"
	CV-2	SCV-2	3/4"
	CV-3	SCV-3	1"
	CV-4	SCV-4	1 1/4"-1 1/2"
	CV-5	SCV-5	2"
	CV-6		2 1/2"-3"
CV-7		3 1/2"-4"	
Gaskets	<b>Neoprene</b>	<b>Composition</b>	
	GKN-1	GKV-1	1/2"
	GKN-2	GKV-2	3/4"
	GKN-3	GKV-3	1"
	GKN-4	GKV-4	1 1/4"-1 1/2"
	GKN-5	GKV-5	2"
	GKN-6	GKV-6	2 1/2"-3"
GKN-7	GKV-7	3 1/2"-4"	



*The D-PAK™ Merchandising System attracts attention with bold graphics and encourages self service with clean, easy-to-read labels*

- Bold red, black, and white descriptive merchandising labels
- Labor saving 2 piece carton
- Combination pack of conduit body, cover and gasket
- Choice of finish: silver, bronze or white
- English, Spanish, and French instructions
- Protective see-through wrap

**Conduit Bodies with Covers and Gaskets**

Catalog No.      Catalog No.      Hub Size

**Through Feed**



Hub Size	Catalog No.	Catalog No.
V 3/4" 1"	<b>Rigid IMC</b> (Raintight)	EMT
	DAC-1-CG	
	DAC-2-CG	
	DAC-3-CG	

**Back Opening**



Hub Size	Catalog No.	Catalog No.
V 3/4" 1" 1 1/4" 1V 2"	DALB-1-CG	•DBLB-1-C
	DALB-2-CG	•DBLB-2-C
	DALB-3-CG	•DBLB-3-C
	DALB-4-CG	
	DALB-5-CG	
	DALB-6-CG	

**Left Side Opening**



Hub Size	Catalog No.	Catalog No.
V 3/4" 1"	DALL-1-CG	
	DALL-2-CG	
	DALL-3-CG	

**Right Side Opening**



Hub Size	Catalog No.	Catalog No.
1/2" 3/4" 1"	DALR-1-CG	
	DALR-2-CG	
	DALR-3-CG	

**T-Style**



Hub Size	Catalog No.	Catalog No.
V 3/4" 1"	DAT-1-CG	
	DAT-2-CG	
	DAT-3-CG	

**Service Entrance Bodies**

**Back Opening**



Hub Size	Catalog No.	Catalog No.
V 3/4" 1"	DASLB-1	
	DASLB-2	
	DASLB-3	

**Boxes**

**Single Gang** - with mounting lugs, two plugs and ground screw

Catalog No.      Hub Size      Color      Outlets

**Three Outlets**



DIH3-1-LM	1/2"	Silver	Top	1
DIH3-1-LM-BR	1/2"	Bronze	Bottom	1
DIH3-1-LM-WH	1/2"	White	Back	1
DIH3-2-LM	3/4"	Silver	Total	3

**Four Outlets**



DIH4-2-LM	1/2"	Silver	Top	2
DIH4-1-LM-BR	1/2"	Bronze	Bottom	1
DIH4-1-LM-WH	1/2"	White	Back	1
DIH4-2-LM	3/4"	Silver	Total	4


**Five Outlets**



DIH5-1-LM	1/2"	Silver	Top	2
DIH5-2-LM	3/4"	Silver	Bottom	2
			Back	1
			Total	5

**Two Gang** - with mounting lugs, two plugs and ground screw

**Three Outlets**



D2IH3-1	1/2"	Silver	Top	1
			Bottom	1
			Back	1
			Total	3

**Round** - with cast mounting lugs, four plugs and ground screw

**Five Outlets**



DS-47	1/2"	Silver	Side	4
DS-47-BR	1/2"	Bronze	Bottom	1
DS-47-WH	1/2"	White	Total	5

• Body and cover only