

Recessed labeling provides easy identification for both installer and user. Helps meet TIA/EIA-606 labeling standard. Labels and protective clear covers (both included) hide mounting screw heads for a clean, fully finished look.

PSF6-OW



Jack modules snap in from the front to make installation fast and simple. Remove jacks from the front without removing the plate for easy reconfiguration.

Provides firm and safe surface for completing terminations. Helps ensure perfect terminations every time.

Fits standard single gang electrical boxes for economical flush-mount application — no special cable boxes required.

Rugged ABS construction for durability. Rated UL 94 V-0.

Dual-style mounting screws for use with either slotted or Phillips™ screwdrivers.




Find jack modules on pages 28-29.


Single and Double Gang Innovate™ Wall Plates

Choose from plates supporting one, two, three, four, six, or eight jack modules. Available in both Off White and our exclusive Light Almond — the perfect match for today's hottest decorated interiors.


Catalog Number	Description	Color	Package	Carton
PSF1-LA PSF1-OW	1-port wall plate single gang	Light Almond Off White	1	10
PSF2-LA PSF2-OW	2-port wall plate single gang	Light Almond Off White	1	10
PSF3-LA PSF3-OW	3-port wall plate single gang	Light Almond Off White	1	10
PSF4-LA PSF4-OW	4-port wall plate single gang	Light Almond Off White	1	10
PSF6-LA PSF6-OW	6-port wall plate single gang	Light Almond Off White	1	10
PSF62-LA PSF62-OW	6-port wall plate double gang	Light Almond Off White	1	10
PSF82-LA PSF82-OW	8-port wall plate double gang	Light Almond Off White	1	10



PSF62



PSF82



PSF1




PSF2



PSF3




PSF4



PSF6

Commercial Network Wiring TradeMaster® DataCom & Innovate™ Wall Plates




TPD4-LA
S58-LA
SFF-LA

Smooth, polished look fits any decor and matches TradeMaster wiring device wall plates. Ideal for any commercial installation where appearance is especially important. And a perfect match for P&S Innovate™ jacks.


Better coverage, with an extra 3/16" more width and height than standard plates to reduce time-consuming drywall rework.

Flexible modular design accepts any combination of P&S Innovate jack modules for fast, easy configuration.


Virtually unbreakable construction features patent-pending reinforcing ribs for enhanced rigidity.



TPD1-LA




TPD9-LA



PSF1




PSF62



PSF82

Catalog Number	Description	Color	Catalog Number	Description	Color
TradeMaster DataCom Wall Plates					
TPD1-GRY TPD1-I TPD1-LA TPD1-W	1-port wall plate, single gang	Gray Ivory Light Almond White	TPD4-GRY TPD4-I TPD4-LA TPD4-W	4-port wall plate, single gang	Gray Ivory Light Almond White
TPD2-GRY TPD2-I TPD2-LA TPD2-W	2-port wall plate, single gang	Gray Ivory Light Almond White	TPD6-GRY TPD6-I TPD6-LA TPD6-W	6-port wall plate, single gang	Gray Ivory Light Almond White
TPD3-GRY TPD3-I TPD3-LA TPD3-W	3-port wall plate, single gang	Gray Ivory Light Almond White	TPD9-GRY TPD9-I TPD9-LA TPD9-W	9-port wall plate, double gang	Gray Ivory Light Almond White

APPLICATION TIP



The perfect match for TradeMaster wiring device wall plates.

Looking to specify network wiring devices that are 100 percent aesthetically compatible with your other wiring devices? Now you can, with the TradeMaster line. The same colors. The same finishes. The same sophisticated contours. The same dimensions. And because TradeMaster power wiring wall plates are available in a full range of colors and types, you don't have to compromise anywhere appearance is important.

- Features**
- Recessed labeling provides easy identification. Helps meet TIA/EIA-606 labeling standard. Labels and protective clear covers (both included) hide mounting screw heads.
 - Jack modules snap in from the front to make installation fast and simple. Remove jacks from the front without removing the plate for easy reconfiguration.
 - Rugged ABS construction for durability. Rated UL94 V0.

Catalog Number	Description	Color
Innovate Wall Plates		
PSF1-LA	1-port wall plate single gang	Light Almond
PSF2-LA	2-port wall plate single gang	Light Almond
PSF3-LA	3-port wall plate single gang	Light Almond
PSF4-LA	4-port wall plate single gang	Light Almond
PSF6-LA	6-port wall plate single gang	Light Almond
PSF62-LA	6-port wall plate double gang	Light Almond
PSF82-LA	8-port wall plate double gang	Light Almond

Commercial Network Wiring TradeMaster® DataCom & Innovate™ Wall Plates




TPD4-LA
S58-LA
SFF-LA

Smooth, polished look fits any decor and matches TradeMaster wiring device wall plates. Ideal for any commercial installation where appearance is especially important. And a perfect match for P&S Innovate™ jacks.


Better coverage, with an extra 3/16" more width and height than standard plates to reduce time-consuming drywall rework.

Flexible modular design accepts any combination of P&S Innovate jack modules for fast, easy configuration.


Virtually unbreakable construction features patent-pending reinforcing ribs for enhanced rigidity.



TPD1-LA




TPD9-LA



PSF1




PSF62



PSF82

Catalog Number	Description	Color	Catalog Number	Description	Color
TradeMaster DataCom Wall Plates					
TPD1-GRY TPD1-I TPD1-LA TPD1-W	1-port wall plate, single gang	Gray Ivory Light Almond White	TPD4-GRY TPD4-I TPD4-LA TPD4-W	4-port wall plate, single gang	Gray Ivory Light Almond White
TPD2-GRY TPD2-I TPD2-LA TPD2-W	2-port wall plate, single gang	Gray Ivory Light Almond White	TPD6-GRY TPD6-I TPD6-LA TPD6-W	6-port wall plate, single gang	Gray Ivory Light Almond White
TPD3-GRY TPD3-I TPD3-LA TPD3-W	3-port wall plate, single gang	Gray Ivory Light Almond White	TPD9-GRY TPD9-I TPD9-LA TPD9-W	9-port wall plate, double gang	Gray Ivory Light Almond White

APPLICATION TIP



The perfect match for TradeMaster wiring device wall plates.

Looking to specify network wiring devices that are 100 percent aesthetically compatible with your other wiring devices? Now you can, with the TradeMaster line. The same colors. The same finishes. The same sophisticated contours. The same dimensions. And because TradeMaster power wiring wall plates are available in a full range of colors and types, you don't have to compromise anywhere appearance is important.

- Features**
- Recessed labeling provides easy identification. Helps meet TIA/EIA-606 labeling standard. Labels and protective clear covers (both included) hide mounting screw heads.
 - Jack modules snap in from the front to make installation fast and simple. Remove jacks from the front without removing the plate for easy reconfiguration.
 - Rugged ABS construction for durability. Rated UL94 V0.

Catalog Number	Description	Color
Innovate Wall Plates		
PSF1-LA	1-port wall plate single gang	Light Almond
PSF2-LA	2-port wall plate single gang	Light Almond
PSF3-LA	3-port wall plate single gang	Light Almond
PSF4-LA	4-port wall plate single gang	Light Almond
PSF6-LA	6-port wall plate single gang	Light Almond
PSF62-LA	6-port wall plate double gang	Light Almond
PSF82-LA	8-port wall plate double gang	Light Almond