
# OMNI-BEAM<sup>™</sup> DC Power Blocks ■ A NINLER




OMNI-BEAM dc power blocks provide regulated low voltage dc power to the sensor head and logic module (if one is used), with input of 10 to 30V dc. There are two infinite-life outputs, one for the load and the other for the alarm of the D.A.T.A. early-warning self-diagnostic system.

All models, except emitter-only types, have the unique Bi-Modal™ output design that offers either sinking (NPN) or sourcing (PNP) outputs, depending upon the polarity with which the two dc supply leads are connected. Outputs are protected from overload, shorted load, or low voltage conditions. Outputs automatically reset when the cause of the problem is cleared. Problems are identified by the D.A.T.A. light system.

All OMNI-BEAM power blocks are epoxy-encapsulated and rated for -40 to +70°C (-40 to +158°F). They feature limit switch style crosshole design for front, back, or side mounting, plus a 30mm threaded hub for swivel bracket or through-hole mounting. Models include prewired cable or either style of quick-disconnect (QD) fitting.

Prewired 6-foot PVC-jacketed 4-conductor cable.		
Integral standard 4-conductor quick-disconnect cable fitting. Requires cable model MBCC-412, sold separately.		
Integral 12mm micro 4-conductor quick-discon- nect cable fitting. Requires micro cable model MQDC-415, sold separately.		
The following three power blocks are for use with emitters only (model OSBE). They contain no output circuitry.		
Prewired 6-foot PVC-jacketed 2-conductor cable.		
Integral standard 4-conductor quick-disconnect cable fitting. Requires cable model MBCC-412, sold separately.		
Integral 12mm micro 4-conductor quick-discon- nect cable fitting. Requires micro cable model MQDC-415, sold separately.		



WHITE

OPRT20

the photoelectric specialist


### Specifications, dc Power Blocks:

Input: 10 to 30V dc at less than 80mA (exclusive of loads), 10% maximum ripple.

Output: two identical open-collector transistors, one for load and one for alarm. Both are configured to either sink (NPN) or source (PNP), depending upon the polarity of the power supply leads (see hookup drawings). 100mA maximum continuous, overload and short circuit protected (both outputs). Off-state leakage current less than 100 microamps. NOTE: interface to TTL logic is not direct (contact factory). NOTE: when the load and the OMNI-BEAM *do not* share a common power supply, load voltage *must* be  $\leq$  the sensor supply voltage.

#### On-state Voltage Drop:

NPN outputs: <1.0V @10mA load, and <1.5V @100mA load. PNP outputs: <1.0V @10mA load, and <1.5V @100mA load.




BROWN wire to dc common.

Each output sources up to 100mA.

Printed in USA

p/n 03532 Rev. B




## **Quick-disconnect** Cables for OMNI-BEAM DC Power Blocks

Quick-disconnect cables are available in two styles: standard SO-type and micro ST-style. They are ideal for use in situations where it is desireable to be able to substitute or replace the sensor and/or cabling.

OMNI-BEAM dc power blocks use 4-conductor cables.


Standard-style cables are 12 feet long; micro-style cables are 15 feet long. All quick-disconnect cables have 22 AWG conductors. Dimensional information is given in the drawings below.

Power Block Model	Use Cable Model
OPBT2QD OPBTEQD	MBCC-412
OPBT2QDH OPBTEQDH	MQDC-415




## SMB30MM Mounting Bracket

Accessory mounting bracket model SMB30MM has curved mounting slots for versatility in mounting and orientation. The OMNI-BEAM mounts to the bracket by its threaded base, using a jam nut and lockwasher (supplied). The curved mounting slots have clearance for 1/4-inch screws. Bracket material is 11-gauge stainless steel.



### SMB30MM Dimensions (ac sensor shown)



WARRANTY: Banner Engineering Corporation warrants its products to be free from defects for one year. Banner Engineering Corporation will repair or replace, free of charge, any product of its manufacture found to be defective at the time it is returned to the factory during the warranty period. This warranty does not cover damage or liability for the improper application of Banner products. This warranty is in lieu of any other warranty either expressed or implied.

# **Banner Engineering Corp Limited Warranty**

Banner Engineering Corp. warrants its products to be free from defects in material and workmanship for one year following the date of shipment. Banner Engineering Corp. will repair or replace, free of charge, any product of its manufacture which, at the time it is returned to the factory, is found to have been defective during the warranty period. This warranty does not cover damage or liability for misuse, abuse, or the improper application or installation of the Banner product.

THIS LIMITED WARRANTY IS EXCLUSIVE AND IN LIEU OF ALL OTHER WARRANTIES WHETHER EXPRESS OR IMPLIED (INCLUDING, WITHOUT LIMITATION, ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE), AND WHETHER ARISING UNDER COURSE OF PERFORMANCE, COURSE OF DEAL-ING OR TRADE USAGE.

This Warranty is exclusive and limited to repair or, at the discretion of Banner Engineering Corp., replacement. IN NO EVENT SHALL BANNER ENGINEERING CORP. BE LIABLE TO BUYER OR ANY OTHER PERSON OR ENTITY FOR ANY EXTRA COSTS, EXPENSES, LOSSES, LOSS OF PROFITS, OR ANY INCIDENTAL, CONSEQUENTIAL OR SPECIAL DAMAGES RESULTING FROM ANY PRODUCT DEFECT OR FROM THE USE OR INABILITY TO USE THE PRODUCT, WHETHER ARISING IN CONTRACT OR WARRANTY, STATUTE, TORT, STRICT LIABILITY, NEGLIGENCE, OR OTHERWISE.

Banner Engineering Corp. reserves the right to change, modify or improve the design of the product without assuming any obligations or liabilities relating to any product previously manufactured by Banner Engineering Corp.



P/N 03532 Rev. B