



## Customer Specification #390T Technicians

### PRODUCT NOMENCLATURE

Manufacturing Glove Code: #390T  
Manufacturing Glove Name: Technicians – Light Duty Neoprene/Natural Latex Blend  
Marketing Glove ASPN Code(s): (7) 193951 (8) 193953 (9) 193955 (10) 193957 (11) 193958

### PRODUCT DESCRIPTION

|                         |  |                  |                                     |
|-------------------------|--|------------------|-------------------------------------|
| Product Classification: | <b>Chemical Resistant (Unsupported)</b>                              | Lining:          | <b>Unlined, Chlorinated</b>         |
| Exterior Color:         | <b>Natural</b>   | Exterior Finish: | <b>Chlorinated</b>                  |
| Former Pattern Style:   | <b>Pebble Grip</b>   | Cuff Finish:     | <b>Pinked</b>                       |
| Coating Composition:    | <b>Neoprene/Natural Rubber Latex Blend</b>                           | Printing:        | <b>Inkjet Black</b>                 |
| Available Sizes:        | <b>7, 8, 9, 10 and 11</b>  | Length:          | <b>305 ± 10 mm (12.1 ± 0.4 in.)</b> |
| Packaging:              | <b>12 Pairs per inner bag<br/>12 Inner bags per case (144 Pairs)</b> |                  |                                     |

### OUTSTANDING CHARACTERISTICS & APPLICATIONS

- ◆ Combines mid-level dexterity and sensitivity with modern chemical protection at an economical price.
- ◆ Pebble-embossed design provides added grip on wet or dry surfaces.
- ◆ Unique blend of neoprene and natural latex combines durability and chemical resistance.
- ◆ **APPLICATIONS:** *Poultry and food processing, Chemical manufacturing and processing, Pharmaceutical manufacturing, Intricate parts assembly, Aerospace, Laboratory*

### REGULATORY COMPLIANCES

- ◆ Complies with FDA regulation 21 CFR 177.2600 for food contact applications.

### TYPICAL PERFORMANCE VALUES

- |                      |                                       |            |
|----------------------|---------------------------------------|------------|
| ◆ Thickness          | 13 ± 2 mils (0.33 ± 0.05 mm)          | ASTM D 412 |
| ◆ Tensile Strength   | > 1900 psi (> 13 Mpa)                 | ASTM D 412 |
| ◆ 300% Modulus       | 290 psi (2 Mpa)                       | ASTM D 412 |
| ◆ Elongation @ Break | > 600%                                | ASTM D 412 |
| ◆ Tear Strength      | Performance Level 1 (10 - 25 newtons) | EN 388     |

### DEFECTS

DEFINITIONS: **Major Defects** are imperfections which *will* result in the failure of the glove to perform it's intended purpose, cause user discomfort or be cosmetically objectionable. **(AQL- 0.65%)**  
**Minor Defects** *may* cause user discomfort or be cosmetically objectionable. **(AQL- 1.5%)**

MAJOR DEFECTS: **Holes/Splits/Tears/Thin Spots/Porosity**

MINOR DEFECTS: **Blisters/Runs/Lumps/Webs/Stains/Creases/Poor Pinking/Ink Smear**

### GENERAL INFORMATION

**SHELF LIFE:** Three (3) years in cool, covered conditions. Extended exposure to direct sunlight or excessive heat will reduce shelf life and result in fading, discoloration and cracking.

**CAUTION:** *This product contains natural rubber latex which may cause allergic reactions in some individuals.*

|                                 |                       |                    |
|---------------------------------|-----------------------|--------------------|
| <b>Originator:</b> Bill Bennett | <b>Date:</b> 02/18/09 | <b>Revision #:</b> |
| <b>Revised By:</b>              | <b>Date:</b>          |                    |

NEITHER THIS NOR ANY STATEMENT MADE BY OR ON BEHALF OF ANSELL HEREIN IS A WARRANTY THAT ANY PRODUCT IS FIT FOR A PARTICULAR PURPOSE, AND ANSELL SHALL NOT BE LIABLE TO ANYONE WITH RESPECT TO THIS INFORMATION.

*This document is the property of Ansell and the information contained herein is proprietary to Ansell.*