

PLUG FUSES

SPECIAL PURPOSE



PLUG FUSES: G/GP/TD/GW/GTL/GT/GSL


Ferraz Shawmut Plug Fuses are for industrial and residential applications. Standard non-time delay fuses are for receptacle and lighting circuits. Standard time delay fuses are for motor loads. For Canadian requirements, a type "P" fuse is used for non-motor loads and type "D" fuses are used for electric heating and cycling loads circuits. Both fuses have low melting-point temperature elements. Low-Temp time delay plug fuses have thermal sensitivity are also for cycling loads and motor circuits. Type "S" plug fuses are time delay and tamper-resistant.

Ratings

- 125V AC, 10kA I.R.
- 3 to 30 Amperes
- Choice of Edison Base, Types "P", "D", or "S"

Approvals

- UL Listed
Guide JEFV, File E76208
- CSA Certified
Class 142301, File 15525



PLUG FUSES – Standard Fuse Ampere Ratings, Catalog Numbers

AMPERE RATING	CATALOG NUMBER						
	EDISON BASE						TYPE S
	Non-Time Delay UL	Non-Time Delay CSA	Time Delay UL	"P" Type Non-Time Delay CSA	Low-Temp Time-Delay UL	"D" Type Time Delay CSA	Rejection* Time Delay UL
3	GW3	G3	-	-	-	-	-
6	GW6	G6	-	-	-	-	-
10	GW10	G10	-	-	-	-	-
15	GW15	-	GTL15	GP15	GT15	TD15	GSL15
20	GW20	-	GTL20	GP20	GT20	TD20	GSL20
25	GW25	-	GTL25	GP25	GT25	TD25	GSL25
30	GW30	-	GTL30	GP30	GT30	TD30	GSL30

FR15, FR20 Rejector Rings available

FRW Rejection tool available

*Must be used with an adaptor to fit an Edison base fuse holder order SAG 15,20,30