

## **▲ LONG CUFF NITRILE EXAM GLOVES**



TEAL **NITRILE NON-STERILE AMBIDEXTROUS FULLY TEXTURED BEADED CUFF** FOR SINGLE USE ONLY **NON-LATEX** 

The long cuff and increased thickness provides an additional level of hand protection for the user. Nitrile offers superior puncture resistance. A textured finish allows for a good grip.

• Longer length and thicker for added protection





PRODUCT CODE				
S	N891			
М	N892			
L	N893			
XL	N894			

PACKAGING			
50	Gloves/Box		
10	Boxes/Case		

GLOVE PROFILE		ASTM D 6319	N89
Length	mm (inches)	min. 220 (8.7)	300 (11.8)
Cuff Thickness	mm (mils)	n/a	0.10 (3.9)
Palm Thickness	mm (mils)	min. 0.05 (2.0)	0.15 (5.9)
Finger Thickness	mm (mils)	min. 0.05 (2.0)	0.18 (7.1)
Tensile Strength	Before Aging After Aging	min. 14 min. 14	27 14
Elasticity/Elongation	Before Aging After Aging	min. 500 min. 400	500 400
Pinhole Defect Rate*	(AQL)	max. 2.5	1.5

<sup>\*</sup> Pinhole Defect Rate is FDA minimum requirement.









RECOMMENDED **INDUSTRIES** 

