

Zinc Cable & Conduit Connectors

For Armored Cable, Flexible Metal Conduit & Metal Clad Cable

Type DC-5500

Duplex Single Screw, Clamp Type

Use:

To make a termination of flexible metal conduit to a knockout or unthreaded slip hole in a dry location box or enclosure.

Features:

- Furnished with locknuts.
- Male hub NPS

Material/Finish:

Zinc Diecast

Third Party Certification:



UL Listed: E25014





CSA Certified: LR14489

Applicable Third Party Standards:

UL Standard: 514B
CSA Standard: C22.2 No. 18
NEMA: FB-1
Fed. Spec: W-F-406D,
Type 1, Class 1, Style B, Kind D

Trade Size (inches)	Catalog Number	Dimensions in Inches		
		A	B	C
3/8"	DC-5500	1.37	0.38	0.68

* 3/8" fits 1/2" K.O.



Type DC-5500

Note:

DC-5500 is listed for use with 14-2 AWG through 12-2 AWG steel or aluminum armored cable.

DC-5500 is listed for use with 14-2 AWG (nominal O.D. .425") through 10-3 AWG (nominal O.D. .560") aluminum interlocking metal-clad cable and 14-2 AWG (nominal O.D. .430") through 10-3 AWG (nominal O.D. .565") steel interlocking metal-clad cable, 14-2 AWG (nominal O.D. .380") through 10-3 AWG (nominal O.D. .565") continuous corrugated round aluminum metal clad cable, and 14-2 AWG (nominal .250" x .365") through 12-3 (nominal .280" x .525") continuous corrugated rectangular aluminum metal-clad cable.

Type C-510

2-Screw Connectors

Use:

To terminate regular wall steel or aluminum flexible conduit to a 1/2" knockout in a dry box or enclosure.

Features:

- End stopped
- Male hub threads NPS
- Provided with locknut

Material/Finish:

Zinc Diecast

Third Party Certification:



UL Listed: E25014





CSA Certified: LR14489

Applicable Third Party Standards:

UL Standard: 514B
CSA Standard: C22.2 No. 18
NEMA: FB-1
Fed. Spec: W-F-406D,
Type 1, Class 1, Style B, Kind D.

Trade Size (inches)	Catalog Number	Dimensions in Inches		
		A	B	C
3/8"	C-510	0.37	0.82	0.94

* 3/8" fits 1/2" K.O.



Type C-510

Note:

C-510 is listed for use with 3/8" regular wall steel or aluminum flexible conduit.

C-510 is listed for use with 14-2 AWG through 10-2 AWG steel or aluminum armored cable.

C-510 is listed for use with 14-2 AWG (nominal O.D. .406" through 10-3 AWG (nominal O.D. .551") aluminum interlocking metal clad cable and 14-2 AWG (nominal O.D. .450") through 10-3 AWG (nominal O.D. .600") steel interlocking metal-clad cable, 14-2 AWG (nominal O.D. .388") through 10-3 AWG (nominal O.D. .500") continuous corrugated round aluminum metal-clad cable, and 14-2 AWG (nominal .250" x .365") through 12-3 (nominal .280" x .490") continuous corrugated rectangular aluminum metal-clad cable.