


Straight Blade Devices Extra Heavy-Duty Illuminated & Compact Design Straight Blade Receptacles




2 Pole, 3 Wire Grounded 15 & 20A, 125 & 250V



Hospital Grade Duplex Receptacle


Features

- One-piece, nickel-plated brass strap, with integral ground contacts (unground) "locked in" to back body & face. Prevents the strap separating from the face & back body.
- External terminal back wire clamps allow visual indication that all strands of wire are correctly secured.
- Oversized #10 combination deep slotted/phillips head brass terminal & ground screws.
- LED Lamp with solder connection for long durable life (10-12 years)—**exclusive**.
- Back wire clamp on ground terminal for easier installation—**exclusive**.
- Circuit label on face of device allows permanent, positive circuit identification—**exclusive**.
- Impact-resistant nylon face & back body.
- One-piece, nickel-plated triple wipe brass power contacts.
- Line terminals accept #14 - #10 AWG copper-clad conductors.




Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance		
				 UL498	 FSUL WC596-G	 C22.2 42M
LED Illuminated Face Duplex Receptacles Back & Side Wire						
8200-ILI	15 125	Ivory	5-15R	•	•	•
8200-ILRED	15 125	Red	5-15R	•	•	•
8300-ILI	20 125	Ivory	5-20R	•	•	•
8300-ILRED	20 125	Red	5-20R	•	•	•

Features

- Impact resistant nylon face.
- One-piece nickel-plated triple-wipe brass power contacts.
- Easily accessible break-off line contact connecting tab for split circuit wiring.
- Terminal compartments isolated from each other for positive conductor containment.
- Corrosion-resistant, Zinc-plated steel strap is locked in.
- Line terminals accept #14 to #10 AWG copper or copper-clad conductors.
- High strength thermoplastic back body.
- Back wire holes allow entry of conductor insulation partially into body but not into wiring compartment.
- Automatic grounding to metallic boxes.
- Compact design for easy installation.




8200-HI Series

Catalog Number	Rating A. V.	Color	NEMA Config. No.	3rd Party Compliance		
				 UL498	 FSUL WC596-G	 C22.2 42M
Duplex Receptacles - Compact Design Back & Side Wire						
8200-HI	15 125	Ivory	5-15R	•	•	•
8200-HW	15 125	White	5-15R	•	•	•
8200-H	15 125	Brown	5-15R	•	•	•
8200-HGRY	15 125	Gray	5-15R	•	•	•
8200-HRED	15 125	Red	5-15R	•	•	•
8200-HLA	15 125	Lt. Almond	5-15R	•	•	•
8300-HI	20 125	Ivory	5-20R	•	•	•
8300-HW	20 125	White	5-20R	•	•	•
8300-H	20 125	Brown	5-20R	•	•	•
8300-HGRY	20 125	Gray	5-20R	•	•	•
8300-HRED	20 125	Red	5-20R	•	•	•
8300-HLA	20 125	Lt. Almond	5-20R	•	•	•
8300-HICN	20 125	Ivory	5-20RCN	•	•	•
8300-HWCN	20 125	White	5-20RCN	•	•	•
8300-HCN	20 125	Brown	5-20RCN	•	•	•
8300-HREDCN	20 125	Red	5-20RCN	•	•	•

NEW

NEW



NEMA 5-15R



NEMA 5-20R



CANADIAN 5-20RCN



CANADIAN 6-20RCN

All devices listed on this page conform to NEMA WD-1.

* Denotes Canadian catalog number. All Canadian products have Combination Slotted/Robertson Head Brass Screws.