

# solar**edge**

## Single Phase Inverter with HD-Wave Technology for North America

SE3000H-US / SE3800H-US / SE5000H-US /  
SE6000H-US / SE7600H-US / SE10000H-US / SE11400H-US

INVERTERS



### Optimized installation with HD-Wave technology

- Specifically designed to work with power optimizers
- Record-breaking efficiency
- Fixed voltage inverter for longer strings
- Integrated arc fault protection and rapid shutdown for NEC 2014 and 2017, per article 690.11 and 690.12
- UL1741 SA certified, for CPUC Rule 21 grid compliance
- Extremely small
- High reliability without any electrolytic capacitors
- Built-in module-level monitoring
- Outdoor and indoor installation
- Optional: Revenue grade data, ANSI C12.20 Class 0.5 (0.5% accuracy)





# Single Phase Inverter

with HD-Wave Technology for North America

SE3000H-US / SE3800H-US / SE5000H-US /  
SE6000H-US/ SE7600H-US / SE10000H-US / SE11400H-US

	SE3000H-US	SE3800H-US	SE5000H-US	SE6000H-US	SE7600H-US	SE10000H-US	SE11400H-US		
<b>OUTPUT</b>									
Rated AC Power Output	3000	3800 @ 240V 3300 @ 208V	5000	6000 @ 240V 5000 @ 208V	7600	10000	11400	VA	
Max. AC Power Output	3000	3800 @ 240V 3300 @ 208V	5000	6000 @ 240V 5000 @ 208V	7600	10000	11400	VA	
AC Output Voltage Min.-Nom.-Max. (183 - 208 - 229)	-	✓	-	✓	-	-	-	Vac	
AC Output Voltage Min.-Nom.-Max. (211 - 240 - 264)	✓	✓	✓	✓	✓	✓	✓	Vac	
AC Frequency (Nominal)	59.3 - 60 - 60.5 <sup>(1)</sup>								
Maximum Continuous Output Current 208V	-	16	-	24	-	-	-	A	
Maximum Continuous Output Current @240V	12.5	16	21	25	32	42	47.5	A	
GFDI Threshold	1								
Utility Monitoring, Islanding Protection, Country Configurable Thresholds	Yes								
<b>INPUT</b>									
Maximum DC Power @240V	4650	5900	7750	9300	11800	15500	17650	W	
Maximum DC Power @208V Transformer-less, Ungrounded	-	5100	-	7750 Yes	-	-	-		
Maximum Input Voltage	480								
Nominal DC Input Voltage	380								
Maximum Input Current 208V	-	9	-	13.5	-	-	-	Vdc	
Maximum Input Current @240V	8.5	10.5	13.5	16.5	20	27	30.5	Vdc	
Max. Input Short Circuit Current	45								
Reverse-Polarity Protection	Yes								
Ground-Fault Isolation Detection	600µs Sensitivity								
Maximum Inverter Efficiency	99	99.2							
CEC Weighted Efficiency	99								
Nighttime Power Consumption	< 2.5								
<b>ADDITIONAL FEATURES</b>									
Supported Communication Interfaces	RS485, Ethernet, ZigBee (optional), Cellular (optional)								
Revenue Grade Data, ANSI C12.20	Optional <sup>(2)</sup>								
Rapid Shutdown - NEC 2014 and 2017 690.12	Automatic Rapid Shutdown upon AC Grid Disconnect								
<b>STANDARD COMPLIANCE</b>									
Safety	UL1741, UL1741 SA, UL1699B, CSA C22.2, Canadian AFCL according to T.I.L. M-07								
Grid Connection Standards	IEEE1547, Rule 21, Rule 14 (H)								
Emissions	FCC Part 15 Class B								
<b>INSTALLATION SPECIFICATIONS</b>									
AC Output Conduit Size / AWG Range	3/4" minimum / 14-6 AWG					3/4" minimum / 14-4 AWG			
DC Input Conduit Size / # of Strings / AWG Range	3/4" minimum / 1-2 strings / 14-6 AWG					3/4" minimum / 1-3 strings / 14-6 AWG			
Dimensions with Safety Switch (HxWxD)	17.7 x 14.6 x 6.8 / 450 x 370 x 174					21.3 x 14.6 x 7.3 / 540 x 370 x 185			
Weight with Safety Switch	22 / 10	25.1 / 11.4	26.2 / 11.9		38.8 / 17.6			in / mm lb / kg	
Noise	< 25					< 50			
Cooling	Natural Convection					Natural convection			
Operating Temperature Range	-13 to +140 / -25 to +60 <sup>(3)</sup> (-40°F / -40°C option) <sup>(4)</sup>								
Protection Rating	NEMA 3R (Inverter with Safety Switch)								

<sup>(1)</sup> For other regional settings please contact SolarEdge support

<sup>(2)</sup> Revenue grade inverter P/N: SExxxH-US000NNC2

<sup>(3)</sup> For power de-rating information refer to: <https://www.solaredge.com/sites/default/files/se-temperature-derating-note-na.pdf>

<sup>(4)</sup> -40 version P/N: SExxxH-US000NNU4

